

11 LITHIUM BATTERIES / NiCd RECHARGEABLE BATTERIES

11.1 LITHIUM BATTERIES

For These Modules	BP150, BP151, BP152, BP154, ME960, ME963, ME965
Description	Lithium batteries 5 pcs., 3 V / 950 mAh
Model Number	0AC201.9
Storage Storage Time Humidity	max. 3 years at 30 °C 5 to 95 % (non-condensing)

11.2 NiCd RECHARGEABLE BATTERIES

For These Modules	CP152, CP153	
Description	NiCd rechargeable batteries 5 pcs., 3.6 V / 40 mAh	
Model Number	0AC100.9	
Storage	Relative humidity of approx. 60 %	
	Storage Time	Storage Temp.
	Long-term Storage	-40 to +35 °C
	6 Months	-40 to +45 °C
	1 Month	-40 to +55 °C
	1 Week	-40 to +65 °C

12 MEMORY CARDS

The CP260 is equipped with a PCMCIA interface. The PCMCIA memory cards that conform to JEIDA V 4.0 Type I or PCMCIA Standard Release 2.0 supported (max. 3 mm high).

B&R can supply the following Memory cards:

Model Number	Description
0MC111.9	PCMCIA Memory Card, 2 MB FlashPROM
0MC211.9	PCMCIA Memory Card, 2 MB SRAM