

8TB2104.203L-00

1 Order data

Model number	Short description	Figure
	Terminal blocks	
8TB2104.203L-00	4-pin screw clamp terminal block, 1-row, spacing: 5.08 mm, label 3: T- T+ B- B+, coding L: 1010	

Table 1: 8TB2104.203L-00 - Order data

2 Technical data

Model number	8TB2104.203L-00	
Terminal block		
Note	Label 3: T- T+ B- B+ Coding L: 1010 1-row	
Number of pins	4	
Type of terminal block	Screw clamp terminal block	
Cable type	Only copper wires (no aluminum wires!)	
Keying	L	
Spacing	5.08 mm	
Wire stripping length	10 mm	
Connection cross section		
AWG wire	30 to 12 AWG	
Wire end sleeves with plastic covering	0.25 to 2.5 mm ²	
Solid wires	0.2 to 2.5 mm ²	
Fine strand wires	0.2 to 1.5 mm ²	
With wire end sleeves	0.25 to 2.5 mm ²	
Tightening torque	0.5 to 0.6 Nm	
Electrical characteristics		
Nominal voltage	250 V (IEC) / 300 V (UL)	
Nominal current	12 A (IEC) / 15 A (UL)	
Mechanical characteristics		
Dimensions		
Width	20.3 mm	
Height	15 mm	
Depth	18.3 mm	
Weight	3.6 g	

Table 2: 8TB2104.203L-00 - Technical data