

8TB4104.202N-10

1 Order data


Model number	Short description	Figure
	Terminal blocks	
8TB4104.202N-10	4-pin screw clamp, single row, spacing: 10.16 mm, label 2: L1 L2 L3 PE, N keying: 1100	

Table 1: 8TB4104.202N-10 - Order data

2 Technical data

Product ID	8TB4104.202N-10
Terminal block	
Note	Label 2: L1 L2 L3 P3 N keying: 1100 Nominal values according to UL
Number of pins	4
Type of terminal block	Screw clamp terminal block
Cable type	Only copper wires (no aluminum wires!)
Keying	N
Distance between contacts	10.16 mm
Connection cross section	
AWG wire	20 to 6 AWG
Wire end sleeves with plastic covering	0.5 to 10 mm ²
Solid wires	0.75 to 16 mm ²
Fine strand wires	0.75 to 6 mm ²
With wire end sleeves	0.5 to 16 mm ²
Tightening torque	1.7 to 1.8 Nm
Electrical characteristics	
Nominal voltage	600 V
Nominal current	55 A

Table 2: 8TB4104.202N-10 - Technical data