

PPC900

Device number key

	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18
	Group		Automation Panel	Panel version	CPU board	RAM	Cfast slot	Slide-in compact	IF option 1	IF option 2	Bus extension	Operating system	Real time operating system			Version (000 = standard)		
PPC900	5	Z													-	0	0	0
Automation Panel cabinet mounted 10.4" (640x480), single-touch RES (5AP1120.1043-000)			3	C	0													
Automation Panel cabinet mounted 10.4" (640x480), single-touch RES, 22 function keys (5AP1180.1043-000)			3	D	0													
Automation Panel cabinet mounted 10.4" (640x480), single-touch RES, 38 function keys and 20 system keys (5AP1181.1043-000)			3	E	0													
Automation Panel cabinet mounted 10.4" (640x480), single-touch RES, 44 function keys and 20 system keys (5AP1182.1043-000)			3	F	0													
Automation Panel cabinet mounted 10.4" (640x480), single-touch RES, RFID (5AP1125.1043-100)			3	A	I													
Automation Panel cabinet mounted 12.4" (800x600), single-touch RES (5AP1120.1214-000)			4	A	I													
Automation Panel cabinet mounted 10.4" (800x600), single-touch RES, RFID (5AP1125.1044-100)			4	A	I													
Automation Panel cabinet mounted 12.1" (1024x768), single-touch RES (5AP923.1215-00)			5	A	0													
Automation Panel cabinet mounted 15.0" (1024x768), single-touch RES (5AP923.1505-00)			5	B	0													
Automation Panel cabinet mounted 15.0" (1024x768), single-touch RES (5AP1120.1505-000)			5	C	0													
Automation Panel cabinet mounted 15.0" (1024x768), single-touch RES, mit Tasten (5AP1180.1505-000)			5	D	0													
Automation Panel cabinet mounted 15.0" (1024x768), single-touch RES, RFID (5AP1125.1505-100)			5	A	I													
Automation Panel cabinet mounted 12.1" (1024x768), single-touch RES (5AP923.1215-100)			5	B	I													
Automation Panel cabinet mounted 15.0" (1024x768), single-touch RES (5AP923.1505-100)			5	C	I													
Automation Panel cabinet mounted 19.0" (1280x1024), single-touch RES (5AP923.1906-00)			6	A	0													
Automation Panel cabinet mounted 19.0" (1280x1024), single-touch RES (5AP1120.1906-000)			6	B	0													
Automation Panel cabinet mounted 15.6" (1366x768), multi-touch PCT (5AP933.1568-00)			B	A	0													
Automation Panel cabinet mounted 18.5" (1366x768), multi-touch PCT (5AP933.1858-00)			B	B	0													
Automation Panel cabinet mounted 18.5" (1366x768), single-touch RES (5AP1120.1568-000)			B	C	0													
Automation Panel cabinet mounted 21.5" (1920x1080), multi-touch PCT (5AP933.215C-00)			C	A	0													
Automation Panel cabinet mounted 24" (1920x1080), multi-touch PCT (5AP933.240C-00)			C	B	0													
Standard																		
Full customized (incl. mylar versions type "I")																		
Mylar version																		
Industry specific																		
Intel Celeron 1047UE, 1.4 GHz, Dual-Core, without fan (5PC901.TS77-10 & 5PC911.SX00-01)																		1
Intel Celeron 1020E, 2.2 GHz, Dual-Core, without fan (5PC901.TS77-09 & 5PC911.SX00-01)																		2
Intel Celeron 827E, 1.4 GHz, Single-Core, without fan (5PC901.TS77-08 & 5PC911.SX00-01)																		3
Intel Celeron 847E, 1.1 GHz, Dual-Core, without fan (5PC901.TS77-07 & 5PC911.SX00-01)																		4
Intel Core i3-3217UE, 1.6 GHz, Dual Core, without fan (5PC901.TS77-06 & 5PC911.SX00-01)																		5
Intel Core i3-3120ME, 2.4 GHz, Dual Core, without fan (5PC901.TS77-05 & 5PC911.SX00-01)																		6
Intel Core i5-3610ME, 2.7 GHz, Dual-Core, without fan (5PC901.TS77-04 & 5PC911.SX00-01)																		7
Intel Core i7-3517UE, 1.7 GHz, Dual-Core, without fan (5PC901.TS77-03 & 5PC911.SX00-01)																		8
Intel Core i7-3555LE, 2.5 GHz, Quad-Core, without fan (5PC901.TS77-02 & 5PC911.SX00-01)																		9
Intel Core i7-3612QE, 2.1 GHz, Quad-Core, without fan (5PC901.TS77-01 & 5PC911.SX00-01)																		A
Intel Celeron 1047UE, 1.4 GHz, Dual-Core, with fan (5PC901.TS77-00 & 5PC911.SX00-00)																		E
Intel Celeron 1020E, 2.2 GHz, Dual-Core, with fan (5PC901.TS77-01 & 5PC911.SX00-00)																		A
Intel Celeron 827E, 1.4 GHz, Single-Core, with fan (5PC901.TS77-02 & 5PC911.SX00-00)																		F
Intel Celeron 847E, 1.1 GHz, Dual-Core, with fan (5PC901.TS77-03 & 5PC911.SX00-00)																		G
Intel Core i3-3217UE, 1.6 GHz, Dual Core, with fan (5PC901.TS77-04 & 5PC911.SX00-00)																		H
Intel Core i3-3120ME, 2.4 GHz, Dual Core, with fan (5PC901.TS77-05 & 5PC911.SX00-00)																		I
Intel Core i5-3610ME, 2.7 GHz, Dual-Core, with fan (5PC901.TS77-06 & 5PC911.SX00-00)																		J
Intel Core i7-3517UE, 1.7 GHz, Dual-Core, with fan (5PC901.TS77-07 & 5PC911.SX00-00)																		K
Intel Core i7-3555LE, 2.5 GHz, Quad-Core, with fan (5PC901.TS77-08 & 5PC911.SX00-00)																		L
Intel Core i7-3612QE, 2.1 GHz, Quad-Core, with fan (5PC901.TS77-09 & 5PC911.SX00-00)																		M
Intel Core i7-3615QE, 2.3 GHz, Quad-Core, with fan (5PC901.TS77-10 & 5PC911.SX00-00)																		N
DDR3, 1 GB (single channel) (5MMDDR.1024-03)																		P
DDR3, 2 GB (single channel) (5MMDDR.2048-03)																		0
DDR3, 4 GB (single channel) (5MMDDR.4096-03)																		1
DDR3, 8 GB (single channel) (5MMDDR.8192-03)																		2
DDR3, 16 GB (dual channel) (2x5MMDDR.8192-03)																		3
DDR3, 2 GB (dual channel) (2x5MMDDR.1024-03)																		4
DDR3, 4 GB (dual channel) (2x5MMDDR.2048-03)																		7
DDR3, 8 GB (dual channel) (2x5MMDDR.4096-03)																		8
Empty																		9
Cfast 2 GB SLC (5CFAST.2048-00)																		0
Cfast 4 GB SLC (5CFAST.4096-00)																		1
Cfast 8 GB SLC (5CFAST.8192-00)																		2
Cfast 16 GB SLC (5CFAST.016G-00)																		3
Cfast 32 GB SLC (5CFAST.032G-00)																		4
Cfast 32GB MLC (5CFAST.032G-10)																		5
Cfast 64GB MLC (5CFAST.064G-10)																		A
Cfast 128GB MLC (5CFAST.128G-10)																		B
Empty																		C
HDD 500 GB (5AC901.CHDD-01)																		0
SSD 60 GB MLC (5AC901.CSSD-03)																		1
SSD 128 GB MLC (5AC901.CSSD-04)																		2
SSD 256 GB MLC (5AC901.CSSD-05)																		3
SSD 512GB MLC (5AC901.CSSD-06)																		4
Empty																		5
RS232/422/485 (5AC901.I485-00)																		0
CAN interface (5AC901.ICAN-00)																		1
Audio interface (5AC901.IHDA-00)																		2
Ready relay (5AC901.IRDY-00)																		3
UPS interface 4.5 Ah (5AC901.BUPS-00)																		4
UPS interface 2.2 Ah (5AC901.BUPS-01)																		5
System IO (5AC901.ISIO-00)																		6
Empty																		7
RS232/422/485 (5AC901.I485-00)																		0
CAN interface (cannot be combined with CAN on IF1) (5AC901.ICAN-00)																		1
SRAM (5AC901.ISRM-00)																		2
Ready relay (5AC901.IRDY-00)																		3
Powerlink, SRAM (5AC901.IPLK-00)																		4
System IO (5AC901.ISIO-00)																		7
Empty																		8
1 PCI, 1 slide-In (5AC902.BX01-00 & fan if necessary (5AC902.FA0X-00))																		0
1 PCIe, 1 slide-In (5AC902.BX01-01 & fan if necessary (5AC902.FA0X-00))																		1
2 PCI, 1 slide-In (5AC902.BX02-00 & fan if necessary (5AC902.FA0X-00))																		2
1 PCI, 1 PCIe, slide-In (5AC902.BX02-01 & fan if necessary (5AC902.FA0X-00))																		3
2 PCIe, slide-In (5AC902.BX02-02 & fan if necessary (5AC902.FA0X-00))																		4
Without																		5
Microsoft OEM Windows Embedded Standard 7 32-Bit, Service Pack 1, English (pre-installed) (SSWWI7.1541-ENG)																		0
Microsoft OEM Windows Embedded Standard 7 64-Bit, Service Pack 1, English (pre-installed) (SSWWI7.1641-ENG)																		1
Microsoft OEM Windows Embedded Premium 7 32-Bit, Service Pack 1, Multilanguage (pre-installed) (SSWWI7.1741-MUL)																		2
Microsoft OEM Windows Embedded Premium 7 64-Bit, Service Pack 1, Multilanguage (pre-installed) (SSWWI7.1841-MUL)																		3
Microsoft OEM Windows 7 Professional 32-Bit, Service Pack 1, English (enclosed) (SSWWI7.1100-ENG)																		4
Microsoft OEM Windows 7 Professional 64-Bit, Service Pack 1, English (enclosed) (SSWWI7.1200-ENG)																		5
Microsoft OEM Windows 7 Ultimate 32-Bit, Service Pack 1, Multilanguage (enclosed) (SSWWI7.1300-MUL)																		6
Microsoft OEM Windows 7 Ultimate 64-Bit, Service Pack 1, Multilanguage (enclosed) (SSWWI7.1400-MUL)																		7
Microsoft OEM Windows Embedded Standard 2009, English (pre-installed) (SSWWXP.0741-ENG)																		8
Microsoft OEM Windows XP Professional, Service Pack 3, Multilanguage (enclosed) (SSWWXP.0600-MUL)																		9
Microsoft OEM Windows 8.1 Industry Professional 32-Bit, Multilanguage (pre-installed) (SSWWI8.0341-MUL)																		A
Microsoft OEM Windows 8.1 Industry Professional 64-Bit, Multilanguage (pre-installed) (SSWWI8.0441-MUL)																		B
Microsoft OEM Windows 10 IoT Enterprise LTSB 2015 64-Bit, Multilanguage (pre-installed) (SSWWI10.0241-MUL)																		C
Debian 8 32-Bit (pre-installed) (SSWJIN.0541-MUL)																		