

	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18
	Group		Automation Panel		Panel version	CPU board	RAM	Cfast slot	Slide-in compact	IF option 1	IF option 2	Bus extension	Operating system	Real time operating syte			Version (000 = standard)	
PPC900	5	Z													-	0	0	0
Automation Panel cabinet mounted 10.4" (640x480), single-touch RES (SAP1120.1043-000			3	C	0													
Automation Panel cabinet mounted 10.4" (640x480), single-touch RES, 22 function keys (SAP1180.1043-000			3	D	0													
Automation Panel cabinet mounted 10.4" (640x480), single-touch RES, 38 function keys and 20 system keys (SAP1181.1043-000			3	E	0													
Automation Panel cabinet mounted 10.4" (640x480), single-touch RES, 44 function keys and 20 system keys (SAP1182.1043-000			3	F	0													
Automation Panel cabinet mounted 10.4" (640x480), single-touch RES, RFID (SAP1125.1043-100			3	A	1													
Automation Panel cabinet mounted 12.4" (800x600), single-touch RES (SAP1120.1214-000			4	A	0													
Automation Panel cabinet mounted 10.4" (800x600), single-touch RES, RFID (SAP1125.1044-100			4	A	1													
Automation Panel cabinet mounted 12.1" (1024x768), single-touch RES (SAP923.1215-00			5	A	0													
Automation Panel cabinet mounted 15.0" (1024x768), single-touch RES (SAP923.1505-00			5	B	0													
Automation Panel cabinet mounted 15.0" (1024x768), single-touch RES (SAP1120.1505-000			5	C	0													
Automation Panel cabinet mounted 15.0" (1024x768), single-touch RES, mit Tasten (SAP1180.1505-000			5	D	0													
Automation Panel cabinet mounted 15.0" (1024x768), single-touch RES, RFID (SAP1125.1505-100			5	A	1													
Automation Panel cabinet mounted 12.1" (1024x768), single-touch RES (SAP923.1215-100			5	B	1													
Automation Panel cabinet mounted 15.0" (1024x768), single-touch RES (SAP923.1505-100			5	C	1													
Automation Panel cabinet mounted 19.0" (1280x1024), single-touch RES (SAP923.1906-00			6	A	0													
Automation Panel cabinet mounted 19.0" (1280x1024), single-touch RES (SAP1120.1906-000			6	B	0													
Automation Panel cabinet mounted 15.0" (1366x768), multi-touch PCT (SAP933.1568-00			6	A	0													
Automation Panel cabinet mounted 18.5" (1366x768), multi-touch PCT (SAP933.1858-00			6	B	0													
Automation Panel cabinet mounted 18.5" (1366x768), single-touch RES (SAP1120.1568-000			6	C	0													
Automation Panel cabinet mounted 21.5" (1920x1080), multi-touch PCT (SAP933.215C-00			C	A	0													
Automation Panel cabinet mounted 24" (1920x1080), multi-touch PCT (SAP933.240C-00			C	B	0													
Standard					0													
Full customized (incl. mylar versions type "T")					C													
Mylar version					F													
Industry specific					I													
Intel Celeron 1047UE, 1.4 GHz, Dual-Core, without fan (5PC901.TS77-10 & 5PC911.SX00-01)						1												
Intel Celeron 1020E, 2.2 GHz, Dual-Core, without fan (5PC901.TS77-09 & 5PC911.SX00-01)						2												
Intel Celeron 827E, 1.4 GHz, Single-Core, without fan (5PC901.TS77-08 & 5PC911.SX00-01						3												
Intel Celeron 847E, 1.1 GHz, Dual-Core, without fan (5PC901.TS77-07 & 5PC911.SX00-01						4												
Intel Core i3-3217UE, 1.6 GHz, Dual-Core, without fan (5PC901.TS77-06 & 5PC911.SX00-01)						5												
Intel Core i3-3120ME, 2.4 GHz, Dual-Core, without fan (5PC901.TS77-05 & 5PC911.SX00-01						6												
Intel Core i5-3610ME, 2.7 GHz, Dual-Core, without fan (5PC901.TS77-04 & 5PC911.SX00-01						7												
Intel Core i7-3517UE, 1.7 GHz, Dual-Core, without fan (5PC901.TS77-03 & 5PC911.SX00-01						8												
Intel Core i7-3612QE, 2.1 GHz, Quad-Core, without fan (5PC901.TS77-01 & 5PC911.SX00-01)						A												
Intel Core i7-3615QE, 2.3 GHz, Quad-Core, with fan (5PC901.TS77-00 & 5PC911.SX00-00						E												
Intel Core i7-3612QE, 2.1 GHz, Quad-Core, with fan (5PC901.TS77-01 & 5PC911.SX00-00						F												
Intel Core i7-3517UE, 1.7 GHz, Dual-Core, with fan (5PC901.TS77-03 & 5PC911.SX00-00						H												
Intel Core i5-3610ME, 2.7 GHz, Dual-Core, with fan (5PC901.TS77-04 & 5PC911.SX00-00						I												
Intel Core i3-3120ME, 2.4 GHz, Dual-Core, with fan (5PC901.TS77-05 & 5PC911.SX00-00						J												
Intel Core i3-3217UE, 1.6 GHz, Dual-Core, with fan (5PC901.TS77-06 & 5PC911.SX00-00						K												
Intel Celeron 847E, 1.1 GHz, Dual-Core, with fan (5PC901.TS77-07 & 5PC911.SX00-00						L												
Intel Celeron 827E, 1.4 GHz, Single-Core, with fan (5PC901.TS77-08 & 5PC911.SX00-00						M												
Intel Celeron 1020E, 2.2 GHz, Dual-Core, with fan (5PC901.TS77-09 & 5PC911.SX00-00						N												
Intel Celeron 1047UE, 1.4 GHz, Dual-Core, with fan (5PC901.TS77-10 & 5PC911.SX00-00						P												
DDR3, 1 GB (single channel) (5MMDDR.1024-03							0											
DDR3, 2 GB (single channel) (5MMDDR.2048-03							1											
DDR3, 4 GB (single channel) (5MMDDR.4096-03							2											
DDR3, 8 GB (single channel) (5MMDDR.8192-03							3											
DDR3, 16 GB (dual channel) (2x5MMDDR.8192-03							4											
DDR3, 2 GB (dual channel) (2x5MMDDR.1024-03							7											
DDR3, 4 GB (dual channel) (2x5MMDDR.2048-03							8											
DDR3, 8 GB (dual channel) (2x5MMDDR.4096-03							9											
Empty								0										
Cfast 2 GB SLC (5CFAST.2048-00)								1										
Cfast 4 GB SLC (5CFAST.4096-00)								2										
Cfast 8 GB SLC (5CFAST.8192-00)								3										
Cfast 16 GB SLC (5CFAST.016G-00)								4										
Cfast 32 GB SLC (5CFAST.032G-00)								5										
Cfast 32GB MLC (5CFAST.032G-10)								A										
Cfast 64GB MLC (5CFAST.064G-10)								B										
Cfast 128GB MLC (5CFAST.128G-10)								C										
Empty									0									
HDD 500 GB (5AC901.CHDD-01)									1									
SSD 60 GB MLC (5AC901.CSSD-03)									2									
SSD 128 GB MLC (5AC901.CSSD-04)									3									
SSD 256 GB MLC (5AC901.CSSD-05)									4									
SSD 512GB MLC (5AC901.CSSD-06)									5									
Empty										0								
RS232/422/485 (5AC901.I485-00)									1									
CAN interface (5AC901.ICAN-00)									2									
Audio interface (5AC901.IHDA-00)									3									
Ready relay (5AC901.IRDY-00)									4									
UPS interface 4.5 Ah (5AC901.BUPS-00)									5									
UPS interface 2.2 Ah (5AC901.BUPS-01)									6									
System IO (5AC901.ISIO-00)									8									
Empty										0								
RS232/422/485 (5AC901.I485-00)									1									
CAN interface (cannot be combined with CAN on IF1) (5AC901.ICAN-00)									2									
SRAM (5AC901.ISRM-00)									3									
Ready relay (5AC901.IRDY-00)									4									
Powerlink, SRAM (5AC901.IPLX-00)									7									
System IO (5AC901.ISIO-00)									8									
Ethernet (5AC901.IETH-00)									9									
Empty											0							
1 PCI, 1 slide-in (5AC902.BX01-00 & fan if necessary (5AC902.FA0X-00))											1							
1 PCIe, 1 slide-in (5AC902.BX01-01 & fan if necessary (5AC902.FA0X-00))											2							
2 PCI, 1 slide-in (5AC902.BX02-00 & fan if necessary (5AC902.FA0X-00))											3							
1 PCI, 1 PCIe, slide-in (5AC902.BX02-01 & fan if necessary (5AC902.FA0X-00))											4							
2 PCIe, slide-in (5AC902.BX02-02 & fan if necessary (5AC902.FA0X-00))											5							
Without															0			
Microsoft OEM Windows Embedded Standard 7 32-Bit, Service Pack 1, English (pre-installed) (5SWWW17.1541-ENG															1			
Microsoft OEM Windows Embedded Standard 7 64-Bit, Service Pack 1, English (pre-installed) (5SWWW17.1641-ENG															2			
Microsoft OEM Windows Embedded Premium 7 32-Bit, Service Pack 1, Multilanguage (pre-installed) (5SWWW17.1741-MUI															3			
Microsoft OEM Windows Embedded Premium 7 64-Bit, Service Pack 1, Multilanguage (pre-installed) (5SWWW17.1841-MUI															4			
Microsoft OEM Windows 7 Professional 32-Bit, Service Pack 1, English (enclosed) (5SWWW17.1100-ENG)															5			
Microsoft OEM Windows 7 Professional 64-Bit, Service Pack 1, English (enclosed) (5SWWW17.1200-ENG)															6			
Microsoft OEM Windows 7 Ultimate 32-Bit, Service Pack 1, Multilanguage (enclosed) (5SWWW17.1300-MUL)															7			
Microsoft OEM Windows 7 Ultimate 64-Bit, Service Pack 1, Multilanguage (enclosed) (5SWWW17.1400-MUL)															8			
Microsoft OEM Windows Embedded Standard 2009, English (pre-installed) (5SWWWXP.0741-ENG															9			
Microsoft OEM Windows XP Professional, Service Pack 3, Multilanguage (enclosed) (5SWWWXP.0600-MUL															A			
Microsoft OEM Windows 8.1 Industry Professional 32-Bit, Multilanguage (pre-installed) (5SWWW8.0341-MUL															B			
Microsoft OEM Windows 8.1 Industry Professional 64-Bit, Multilanguage (pre-installed) (5SWWW8.0441-MUL															C			
Microsoft OEM Windows 10 IoT Enterprise LTSC 2019 64-Bit, Multilanguage (pre-installed) (5SWWW10.0241-MUL															E			
Debian 8 32-Bit (pre-installed) (5SWLIN.0541-MUL)															F			
Debian 8 64-Bit (pre-installed) (5SWLIN.0641-MUL)															G			
Without											</							