

8TB4104.222L-10

1 Order data

Order number	Short description	Figure
	Terminal blocks	
8TB4104.222L-10	4-pin push-in terminal block, 1-row, pitch: 10.16 mm, label 2: PE L3 L2 L1, coding L: 1010	

Table 1: 8TB4104.222L-10 - Order data

2 Technical data

Order number	8TB4104.222L-10
General information	
Short description	Push-in terminal block, 1-row, for 8EI017HWD.../8EI022HWD.../8EI024HWS.../8EI034HWS.../8EI044HWS... servo drives, connector X1 (mains supply)
Certifications	
CE	Yes
UKCA	Yes
UL	cULus E225616 Power conversion equipment
Terminal block	
Note	Label 2: PE L3 L2 L1 Coding L: 1010 1-row
Number of pins	4
Type of terminal block	Push-in spring connector
Cable type	Only copper wires (no aluminum wires!)
Coding	L
Pitch	10.16 mm
Wire stripping length	18 mm
Connection cross section	
AWG wire	20 to 4 AWG
Wire end sleeves with plastic covering	0.75 to 10 mm ²
Single-wire	0.75 to 16 mm ²
Fine-stranded wires	0.75 to 16 mm ²
With wire end sleeves	0.75 to 16 mm ²
Electrical properties	
Nominal voltage	1000 V (IEC) / 600 V (UL)
Nominal current	76 A (IEC) / 66 A (UL)
Mechanical properties	
Dimensions	
Width	40.6 mm
Height	44.5 mm
Depth	25.1 mm
Weight	32 g

Table 2: 8TB4104.222L-10 - Technical data