

8TB4104.202N-00

1 Order data

Model number	Short description	Figure
	Terminal blocks	
8TB4104.202N-00	4-pin screw clamp terminal block, 1-row, spacing: 10.16 mm, label 2: L1 L2 L3 PE, coding N: 1100	

Table 1: 8TB4104.202N-00 - Order data

2 Technical data

Model number	8TB4104.202N-00
Terminal block	
Note	Label 2: L1 L2 L3 P3 Coding N: 1100 1-row
Number of pins	4
Type of terminal block	Screw clamp terminal block
Cable type	Only copper wires (no aluminum wires!)
Keying	N
Spacing	10.16 mm
Wire stripping length	12 mm
Connection cross section	
AWG wire	20 to 8 AWG
Wire end sleeves with plastic covering	0.5 to 6 mm ²
Solid wires	0.75 to 6 mm ²
Fine strand wires	0.75 to 6 mm ²
With wire end sleeves	0.5 to 6 mm ²
Tightening torque	1.2 to 1.5 Nm
Electrical characteristics	
Nominal voltage	1000 V (IEC) / 600 V (UL)
Nominal current	41 A (IEC) / 50 A (UL)
Mechanical characteristics	
Dimensions	
Width	39.7 mm
Height	27.6 mm
Depth	39 mm
Weight	33.2 g

Table 2: 8TB4104.202N-00 - Technical data