

PPC80

Model number key



Product area																	
4														Embedded PC-based Automation			
	Product family																
	P	P													Power Panel		
		Model															
		C														Controller-series	
		Variant															
		8	0													Intel processor (Atom E3940, quad core)	
			Diagonal														
			.	0	5	7											5.7"
			.	0	7	0											7.0"
			.	1	0	1											10.1"
			.	1	2	1											12.1"
		.	1	5	6											15.6"	
			Resolution														
			2														WVGA (800x480)
	3															VGA (640x480)	
	B															HD (1366x768)	
	E															WXGA (1280 x 800)	
			Display / Touch screen technology														
			-	1													TFT color + multi-touch PCT (glass)
			Optional interfaces and features														
			0														Standard / No additional interface
			1														2x CAN
	2															1x RS232, 1x CAN	
	3															1x RS485, 1x CAN	
			Front design														
Standard variants																	
B																Black, clear glass	
A															Black, anti-glare glass		
Industry-specific variant																	
I												Seq. number: I[0...Z][0...Z][0...Z]	
Customized panel overlay only																	
G												Seq. number: G[0...Z][0...Z][0...Z]	
Completely customized variant																	
C												Seq. number: C[0...Z][0...Z][0...Z]	
Examples																	
4	P	P	C	8	0	.	0	5	7	3	-	1	1	B	Power Panel C80, 5.7", glass front, controller with mapp View HMI unit, fieldbus interfaces: 2x CAN bus. CPU and memory of the controller: 1600 MHz (Intel Atom E3940), 4 GB DRAM, 32 kB FRAM, 4 GB onboard flash drive. Display and touch screen: 5.7", 640 x 480 (VGA) resolution, projected capacitive touch screen, multi-touch support, glass front with black frame, landscape and portrait format configurable using software. Interfaces: 1x POWERLINK, 1x Ethernet 10/100/1000 Mbit/s, 1x X2X Link, 2x USB 3.0, 2x CAN bus.		
4	P	P	C	8	0	.	1	2	1	E	-	1	3	A	Power Panel C80, 12.1", glass front (anti-glare), fieldbus interfaces: 1x CAN bus, 1x RS485. CPU and memory: 1600 MHz (Intel Atom E3940), 4 GB DRAM, 64 kB FRAM, 4 GB onboard flash drive. Display and touch screen: 12.1", 1280 x 800 (WXGA) resolution, projected capacitive touch screen, multi-touch support, anti-glare glass front with black frame, landscape and portrait format configurable with software. Interfaces: 1x POWERLINK, 1x Ethernet 10/100/1000 Mbit/s, 1x X2X Link, 2x USB 3.0, 1x CAN bus, 1x RS485.		