

APC2100

Device number key

	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18
	Group		CPU / RAM	CFast slot	IF Option	Display Link Interface	Free	Free	Free	Free	Free	Free	Operating system	Real time operating system		Version (000 = standard)		
APC2100	5	V					0	0	0	0	0	0			-	0	0	0
Intel Atom E3815 1.46 GHz, Single-Core, 1GB			1															
Intel Atom E3825 1.33 GHz, Dual-Core, 1GB			2															
Intel Atom E3826 1.46 GHz, Dual-Core, 2GB			3															
Intel Atom E3827 1.75 GHz, Dual-Core, 4GB			4															
Intel Atom E3845 1.91 GHz, Quad-Core, 4GB			5															
Empty				0														
CFast 2 GB SLC				1														
CFast 4 GB SLC				2														
CFast 8 GB SLC				3														
CFast 16 GB SLC				4														
CFast 32 GB SLC				5														
CFast 32GB MLC				A														
CFast 64GB MLC				B														
CFast 128GB MLC				C														
Empty					0													
Powerlink, FRAM, CAN, RS232					1													
Powerlink, FRAM, RS232 full					2													
SDL/DVI						1												
Without														0				
Microsoft OEM Windows Embedded Standard 7 32-Bit, Service Pack 1, Englisch (pre-installed)														1				
Microsoft OEM Windows Embedded Standard 7 64-Bit, Service Pack 1, Englisch (pre-installed)														2				
Microsoft OEM Windows Embedded Premium 7 32-Bit, Service Pack 1, Multilanguage (pre-installed)														3				
Microsoft OEM Windows Embedded Premium 7 64-Bit, Service Pack 1, Multilanguage (pre-installed)														4				
Microsoft OEM Windows 7 Professional 32-Bit, Service Pack 1, Englisch (enclosed)														5				
Microsoft OEM Windows 7 Professional 64-Bit, Service Pack 1, Englisch (enclosed)														6				
Microsoft OEM Windows 7 Ultimate 32-Bit, Service Pack 1, Multilanguage (enclosed)														7				
Microsoft OEM Windows 7 Ultimate 64-Bit, Service Pack 1, Multilanguage (enclosed)														8				
Microsoft OEM Windows 8.1 Industry Professional 32-Bit, Multilanguage (pre-installed)														9				
Microsoft OEM Windows 8.1 Industry Professional 64-Bit, Multilanguage (pre-installed)														A				
Without														0				
Automation Runtime Windows TG License														1				
Automation Runtime Embedded TG License														2				
Automation Runtime Embedded Terminal TG														3				

