

# APC2100

Device number key

|                                                                                                | 1     | 2 | 3         | 4          | 5              | 6    | 7    | 8    | 9    | 10   | 11   | 12   | 13               | 14                         | 15 | 16 | 17                       | 18 |
|------------------------------------------------------------------------------------------------|-------|---|-----------|------------|----------------|------|------|------|------|------|------|------|------------------|----------------------------|----|----|--------------------------|----|
|                                                                                                | Group |   | CPU / RAM | CFast slot | Link interface | Free | Free | Free | Free | Free | Free | Free | Operating system | Real time operating system |    |    | Version (000 = standard) |    |
| <b>APC2100</b>                                                                                 | 5     | V |           |            |                | 0    | 0    | 0    | 0    | 0    | 0    | 0    |                  |                            | -  | 0  | 0                        | 0  |
| Intel Atom E3815 1.46 GHz, Single-Core, 1GB                                                    |       |   | 1         |            |                |      |      |      |      |      |      |      |                  |                            |    |    |                          |    |
| Intel Atom E3825 1.33 GHz, Dual-Core, 1GB                                                      |       |   | 2         |            |                |      |      |      |      |      |      |      |                  |                            |    |    |                          |    |
| Intel Atom E3826 1.46 GHz, Dual-Core, 2GB                                                      |       |   | 3         |            |                |      |      |      |      |      |      |      |                  |                            |    |    |                          |    |
| Intel Atom E3827 1.75 GHz, Dual-Core, 4GB                                                      |       |   | 4         |            |                |      |      |      |      |      |      |      |                  |                            |    |    |                          |    |
| Intel Atom E3845 1.91 GHz, Quad-Core, 4GB                                                      |       |   | 5         |            |                |      |      |      |      |      |      |      |                  |                            |    |    |                          |    |
| Empty                                                                                          |       |   |           | 0          |                |      |      |      |      |      |      |      |                  |                            |    |    |                          |    |
| CFast 2 GB SLC                                                                                 |       |   |           | 1          |                |      |      |      |      |      |      |      |                  |                            |    |    |                          |    |
| CFast 4 GB SLC                                                                                 |       |   |           | 2          |                |      |      |      |      |      |      |      |                  |                            |    |    |                          |    |
| CFast 8 GB SLC                                                                                 |       |   |           | 3          |                |      |      |      |      |      |      |      |                  |                            |    |    |                          |    |
| CFast 16 GB SLC                                                                                |       |   |           | 4          |                |      |      |      |      |      |      |      |                  |                            |    |    |                          |    |
| CFast 32 GB SLC                                                                                |       |   |           | 5          |                |      |      |      |      |      |      |      |                  |                            |    |    |                          |    |
| CFast 32GB MLC                                                                                 |       |   |           | A          |                |      |      |      |      |      |      |      |                  |                            |    |    |                          |    |
| CFast 64GB MLC                                                                                 |       |   |           | B          |                |      |      |      |      |      |      |      |                  |                            |    |    |                          |    |
| CFast 128GB MLC                                                                                |       |   |           | C          |                |      |      |      |      |      |      |      |                  |                            |    |    |                          |    |
| Empty                                                                                          |       |   |           |            | 0              |      |      |      |      |      |      |      |                  |                            |    |    |                          |    |
| Powerlink, FRAM, CAN, RS232                                                                    |       |   |           |            | 1              |      |      |      |      |      |      |      |                  |                            |    |    |                          |    |
| Powerlink, FRAM, RS232 full                                                                    |       |   |           |            | 2              |      |      |      |      |      |      |      |                  |                            |    |    |                          |    |
| Empty                                                                                          |       |   |           |            |                |      |      |      |      |      |      |      |                  | 0                          |    |    |                          |    |
| Microsoft OEM Windows Embedded Standard 7 32-Bit, Service Pack 1, Englisch (pre-installed)     |       |   |           |            |                |      |      |      |      |      |      |      |                  | 1                          |    |    |                          |    |
| Microsoft OEM Windows Embedded Standard 7 64-Bit, Service Pack 1, Englisch (pre-installed)     |       |   |           |            |                |      |      |      |      |      |      |      |                  | 2                          |    |    |                          |    |
| Microsoft OEM Windows Embedded Premium 7 32-Bit, Service Pack 1, Multilanguage (pre-installed) |       |   |           |            |                |      |      |      |      |      |      |      |                  | 3                          |    |    |                          |    |
| Microsoft OEM Windows Embedded Premium 7 64-Bit, Service Pack 1, Multilanguage (pre-installed) |       |   |           |            |                |      |      |      |      |      |      |      |                  | 4                          |    |    |                          |    |
| Microsoft OEM Windows 7 Professional 32-Bit, Service Pack 1, Englisch (enclosed)               |       |   |           |            |                |      |      |      |      |      |      |      |                  | 5                          |    |    |                          |    |
| Microsoft OEM Windows 7 Professional 64-Bit, Service Pack 1, Englisch (enclosed)               |       |   |           |            |                |      |      |      |      |      |      |      |                  | 6                          |    |    |                          |    |
| Microsoft OEM Windows 7 Ultimate 32-Bit, Service Pack 1, Multilanguage (enclosed)              |       |   |           |            |                |      |      |      |      |      |      |      |                  | 7                          |    |    |                          |    |
| Microsoft OEM Windows 7 Ultimate 64-Bit, Service Pack 1, Multilanguage (enclosed)              |       |   |           |            |                |      |      |      |      |      |      |      |                  | 8                          |    |    |                          |    |
| Microsoft OEM Windows 8.1 Industry Professional 32-Bit, Multilanguage (pre-installed)          |       |   |           |            |                |      |      |      |      |      |      |      |                  | 9                          |    |    |                          |    |
| Microsoft OEM Windows 8.1 Industry Professional 64-Bit, Multilanguage (pre-installed)          |       |   |           |            |                |      |      |      |      |      |      |      |                  | A                          |    |    |                          |    |
| Empty                                                                                          |       |   |           |            |                |      |      |      |      |      |      |      |                  |                            | 0  |    |                          |    |
| Automation Runtime Windows TG License                                                          |       |   |           |            |                |      |      |      |      |      |      |      |                  |                            | 1  |    |                          |    |
| Automation Runtime Embedded TG License                                                         |       |   |           |            |                |      |      |      |      |      |      |      |                  |                            | 2  |    |                          |    |
| Automation Runtime Embedded Terminal TG                                                        |       |   |           |            |                |      |      |      |      |      |      |      |                  |                            | 3  |    |                          |    |

