Field-assembled connectors - I/O supply

1 Order data




Table 1: X67AC0P00, X67AC0P20 - Order data

2 Technical data

Product ID	X67AC0P00	X67AC0P20	
General information			
Connection	Male M8 connector	Female M8 connector	
Keying	-		
Type of terminal clamp	Piercing conn	Piercing connection	
Short description	X67 male M8 connector, 4-pin, piercing connection	X67 female M8 connector, 4-pin, piercing connection	
Number of pins	4-pin	4-pin	
Shielding	-	-	

Table 2: X67AC0P00, X67AC0P20 - Technical data

3 Cable requirements

Product ID	X67AC0P00	X67AC0P20
External diameter of cable	3 - 5 mm	3 - 5 mm
Contact	CuSn	CuSn
Contact surface	Ni/Au	Ni/Au
Flexible connection cross section	0.14 - 0.38 mm²	0.14 - 0.38 mm²
	AWG 26 - 22	AWG 26 - 22

Data sheet V 2.10