

8BPE0001.0000-00

1 Order data

Model number	Short description	Figure
	Accessories	
8BPE0001.0000-00	17-pin EnDat connector, SpeedTec, IP67, crimp contacts included in delivery: 17x 0.14-1.0 mm ² , cable terminals: 6.0 - 10.0 mm, UL/CSA listed	

Table 1: 8BPE0001.0000-00 - Order data

2 Technical data

Model number	8BPE0001.0000-00
General information	
Insulator	PBT, UL 94 / V0
Contacts	Brass / nickel-plated
Protective ground connection on housing	Per VDE 0110/EN 61984, section 6.19.2.2
Certification	UL / CSA
Connector size	Size 1
Number and type of contacts	17 signal contacts
Pollution degree	3
Installation elevation	Up to 2000 m
Protection per DIN 40050	IP66/67 when connected
Electrical characteristics	
Overvoltage category	III
Signal contacts	
Contact resistance	<5 mΩ
Nominal voltage	125 V (AC/DC)
Nominal current	Max. 7 A
Test voltage (L - L)	2000 V
Mechanical characteristics	
Housing	
Material	Zinc casting / nickel plated
Dimensions	
Length	58 mm
Diameter	26 mm
Weight	56 g
Crimp range	17 x 0.06 - 1 mm ²
Gasket	FKM
Connection cycles	>500
Cable terminals	6 - 10 mm
Temperature range	-20°C to +130°C

Table 2: 8BPE0001.0000-00 - Technical data

Information:

Using B&R connectors guarantees that the EMC limits for the connection are not exceeded. Make sure that connectors are assembled correctly and include a proper shield connection.