

8TB2104.203F-00

1 Order data

Model number	Short description	Figure
	Terminal blocks	
8TB2104.203F-00	4-pin screw clamp terminal block, 1-row, spacing: 5.08 mm, label 3: T- T+ B- B+, coding F: 0101	

Table 1: 8TB2104.203F-00 - Order data

2 Technical data

Model number	8TB2104.203F-00
Terminal block	
Note	Label 3: T- T+ B- B+ Coding F: 0101 1-row
Number of pins	4
Type of terminal block	Screw clamp terminal block
Cable type	Only copper wires (no aluminum wires!)
Keying	F
Spacing	5.08 mm
Wire stripping length	10 mm
Connection cross section	
AWG wire	30 to 12 AWG
Wire end sleeves with plastic covering	0.25 to 2.5 mm ²
Solid wires	0.2 to 2.5 mm ²
Fine strand wires	0.2 to 1.5 mm ²
With wire end sleeves	0.25 to 2.5 mm ²
Tightening torque	0.5 to 0.6 Nm
Electrical characteristics	
Nominal voltage	250 V (IEC) / 300 V (UL)
Nominal current	12 A (IEC) / 15 A (UL)
Mechanical characteristics	
Dimensions	
Width	20.3 mm
Height	15 mm
Depth	18.3 mm
Weight	3.6 g

Table 2: 8TB2104.203F-00 - Technical data