

8TB2108.2010-00

1 Order data

Model number	Short description	Figure
	Terminal blocks	
8TB2108.2010-00	8-pin screw clamp terminal block, 1-row, spacing: 5.08 mm, label 1: Numbered consecutively	

Table 1: 8TB2108.2010-00 - Order data

2 Technical data

Model number	8TB2108.2010-00
Terminal block	
Note	Label 1: Numbered consecutively Coding 0: None 1-row
Number of pins	8
Type of terminal block	Screw clamp terminal block
Cable type	Only copper wires (no aluminum wires!)
Keying	0
Spacing	5.08 mm
Wire stripping length	10 mm
Connection cross section	
AWG wire	30 to 12 AWG
Wire end sleeves with plastic covering	0.25 to 2.5 mm ²
Solid wires	0.2 to 2.5 mm ²
Fine strand wires	0.2 to 1.5 mm ²
With wire end sleeves	0.25 to 2.5 mm ²
Tightening torque	0.5 to 0.6 Nm
Electrical characteristics	
Nominal voltage	250 V (IEC) / 300 V (UL)
Nominal current	12 A (IEC) / 15 A (UL)
Mechanical characteristics	
Dimensions	
Width	40.6 mm
Height	15 mm
Depth	27.2 mm
Weight	23.9 g

Table 2: 8TB2108.2010-00 - Technical data