

8TB2112.2010-00

1 Order data

Model number	Short description	Figure
	Terminal blocks	
8TB2112.2010-00	12-pin screw clamp terminal block, 1-row, spacing: 5.08 mm, label 1: Numbered consecutively	

Table 1: 8TB2112.2010-00 - Order data

2 Technical data

Model number	8TB2112.2010-00	
Terminal block		
Note	Label 1: Numbered consecutively Coding 0: None 1-row	
Number of pins	12	
Type of terminal block	Screw clamp terminal block	
Cable type	Only copper wires (no aluminum wires!)	
Keying	0	
Spacing	5.08 mm	
Wire stripping length	10 mm	
Connection cross section		
AWG wire	30 to 12 AWG	
Wire end sleeves with plastic covering	0.25 to 2.5 mm ²	
Solid wires	0.2 to 2.5 mm ²	
Fine strand wires	0.2 to 1.5 mm ²	
With wire end sleeves	0.25 to 2.5 mm ²	
Tightening torque	0.5 to 0.6 Nm	
Electrical characteristics		
Nominal voltage	250 V (IEC) / 300 V (UL)	
Nominal current	12 A (IEC) / 15 A (UL)	
Mechanical characteristics		
Dimensions		
Width	61 mm	
Height	15 mm	
Depth	27.2 mm	
Weight	35.2 g	

Table 2: 8TB2112.2010-00 - Technical data