

8TB3102.201C-11

1 Order data

Model number	Short description	Figure
	Terminal blocks	
8TB3102.201C-11	2-pin screw clamp terminal block, 1-row, spacing: 7.62 mm, label 1: Numbered consecutively, coding C: 10	

Table 1: 8TB3102.201C-11 - Order data

2 Technical data

Model number	8TB3102.201C-11
Terminal block	
Note	Label 1: Numbered consecutively Coding C: 10 1-row
Number of pins	2
Type of terminal block	Screw clamp terminal block
Cable type	Only copper wires (no aluminum wires!)
Keying	C
Spacing	7.62 mm
Wire stripping length	10 mm
Connection cross section	
AWG wire	24 to 8 AWG
Wire end sleeves with plastic covering	0.25 to 4 mm ²
Solid wires	0.2 to 6 mm ²
Fine strand wires	0.2 to 4 mm ²
With wire end sleeves	0.25 to 6 mm ²
Tightening torque	0.7 to 0.8 Nm
Electrical characteristics	
Nominal voltage	1000 V (IEC) / 600 V (UL)
Nominal current	41 A (IEC/UL)
Mechanical characteristics	
Dimensions	
Width	15.2 mm
Height	19.7 mm
Depth	35.3 mm
Weight	9.4 g

Table 2: 8TB3102.201C-11 - Technical data