8TB3104.201H-11

1 Order data

Model number	Short description	Figure
	Terminal blocks	
8TB3104.201H-11	4-pin screw clamp terminal block, 1-row, spacing: 7.62 mm, label 1: Numbered consecutively, coding H: 1110	

Table 1: 8TB3104.201H-11 - Order data

2 Technical data

Model number	8TB3104.201H-11
Terminal block	
Note	Label 1: Numbered consecutively Coding H: 1110 1-row
Number of pins	4
Type of terminal block	Screw clamp terminal block
Cable type	Only copper wires (no aluminum wires!)
Keying	H
Spacing	7.62 mm
Wire stripping length	10 mm
Connection cross section	
AWG wire	24 to 8 AWG
Wire end sleeves with plastic covering	0.25 to 4 mm²
Solid wires	0.2 to 6 mm²
Fine strand wires	0.2 to 4 mm²
With wire end sleeves	0.25 to 6 mm²
Tightening torque	0.7 to 0.8 Nm
Electrical characteristics	
Nominal voltage	1000 V (IEC) / 600 V (UL)
Nominal current	41 A (IEC/UL)
Mechanical characteristics	
Dimensions	
Width	30.4 mm
Height	19.7 mm
Depth	35.3 mm
Weight	3.3 g

Table 2: 8TB3104.201H-11 - Technical data