

8BCR0020.11120-0

1 General information

- Can be used in cable drag chains
- Assembled specifically for 8BCRxxxx.1111A-0 resolver cables
- speedtec - Innovative connector system for secure connections

2 Order data

Order number	Short description	Figure
8BCR0020.11120-0	Resolver cables Cable extension for resolver cable with speedtec or standard connector, length 20 m, can be used in cable drag chains	

Table 1: 8BCR0020.11120-0 - Order data

3 Technical data

Order number	8BCR0020.11120-0
General information	
Cable cross section	3x 2x 24 19 AWG
Durability	Oil resistance per VDE 0472 Part 803 as well as standard hydraulic oils ¹⁾
Certifications	
CE	Yes
UKCA	Yes
UL	cULus E225616 Power conversion equipment
Cable construction	
Signal line	
Quantity	6
Wire insulation	Special thermoplastic material
Wire colors	White/Brown, green/yellow, gray/pink
Variant	Tinned copper stranded wire
Cross section	24 AWG / 19 AWG
Shield	No
Stranding	White with brown, green with yellow, gray with pink
Cable stranding	The 3 pairs together covered by foil shield
Cable shield	Copper braiding, optical coverage ≥90% and foil shield
Outer jacket	
Material	PUR
Color	Green, similar to RAL 6018 flat
Connector	
Type	12-pin female speedtec circular connector
Mating cycles	<500
Contacts	12
Additional connectors	12-pin male coupling Mating cycles: <500 Contacts: 12 Degree of protection per EN 60529: IP66/67 when connected
Degree of protection per EN 60529	IP66/67 when connected
Electrical properties ¹⁾	
Operating voltage	≤30 V _{eff}
Test voltage	
Wire - Wire	1.5 kV
Wire - Shield	0.8 kV
Conductor resistance	
Signal line	≤86 Ω/km
Insulation resistance	>200 MΩ*km
Ambient conditions ¹⁾	
Temperature	
Moving	-20°C to +80°C
Static	-20°C to +90°C

Table 2: 8BCR0020.11120-0 - Technical data

Order number	8BCR0020.11120-0
Mechanical properties ¹⁾	
Dimensions	
Length	20 m
Diameter	6.5 mm ±0.2 mm
Bend radius	
Single bend	≥20 mm
Moving	≥50 mm
Drag chain data	
Acceleration	≤6 g
Flex cycles ²⁾	>3,000,000
Velocity	≤4 m/s
Weight	1.4 kg

Table 2: 8BCR0020.11120-0 - Technical data

- 1) Values refer to the raw cable being used.
2) At an ambient temperature of 20°C and bend radius of 65 mm.

4 Wiring

4.1 Cable construction


		
Pos.	Description	Note
1	Encoder line	3x 2x 24 AWG/19
2	12-pin female circular connector	
3	12-pin male coupling	

Table 3: 8BCR cable extension - Construction

4.2 Pinout



Circular connector	Pin	Description	Function	Pin	Coupling
	1	---		1	
	2	---		2	
	3	Sin	Sine input	3	
	4	Cos\	Cosine input inverted	4	
	5	Ref	Reference output	5	
	6	---		6	
	7	Sin\	Sine input inverted	7	
	8	Cos	Cosine input	8	
	9	Ref\	Reference output inverted	9	
	10	---		10	
	11	---		11	
	12	---		12	

Table 4: 8BCR cable extension - Pinout

4.3 Cable diagram




Figure 1: 8BCR cable extension - Cable diagram