

8CM025.12-0

1 General information

- UL/CSA certified
- Can be used in cable drag chains
- Optimally produced for use with ACOPOS 1010/1016/1022/1045/1090 servo drives and B&R servo motors with size 1 motor connectors

2 Order data

Model number	Short description	Figure
	0.75 mm² motor cables	
8CM025.12-0	Motor cable, length 25 m, 4x 0.75 mm ² + 2x 2x 0.35 mm ² , 8-pin female Intercontec motor connector, can be used in drag chains, UL/CSA listed	

Table 1: 8CM025.12-0 - Order data

3 Technical data

Product ID	8CM025.12-0
General information	
Cable cross section	4x 0.75 mm ² + 2x 2x 0.35 mm ²
Durability	Oil resistance according to VDE 0472 part 803 as well as standard hydraulic oil
Listed	UL AWM Style 20234, 80°C, 1000 V, E63216 and CSA AWM I/II A/B, 90°C, 1000 V, FT2 LL46064
Certification	
CE	Yes
cULus	Yes
Cable construction	
Power lines	
Quantity	4
Wire insulation	Special thermoplastic material
Wire colors	Black, brown, blue, yellow/green
Design	Tinned copper stranded wire
Diameter	0.75 mm ²
Shield	No
Stranding	No
Signal lines	
Quantity	4
Wire insulation	Special thermoplastic material
Wire colors	White, white/red, white/blue, white/green
Design	Tinned copper stranded wire
Diameter	0.35 mm ²
Shield	Separate shielding for pairs, tinned copper braiding, optical coverage >85% and foil banding
Stranding	White with white/red and white/blue with white/green
Cable stranding	With filler elements and foil banding
Complete shielding	Tinned copper braiding, optical coverage >85% and wrapped in isolating film
Outer sheathing	
Material	PUR
Color	Orange, similar to RAL 2003 flat
Labeling	BERNECKER + RAINER 4x0.75+2x2x0.35 FLEX UL AWM STYLE 20234 80°C 1000 V E63216 CSA AWM I/II A/B 90°C 1000 V FT2 LL46064
Connector	
Type	Intercontec 8-pin female motor connector
Connection cycles	>50
Contacts	8 (4 power and 4 signal contacts)
EN 60529 protection	IP67 when connected
Electrical characteristics	
Test voltage	
Wire/Wire	3 kV
Wire/Shield	3 kV

Table 2: 8CM025.12-0 - Technical data

Product ID	8CM025.12-0
Conductor resistance	
Power lines	≤0.73 Ω
Signal lines	≤1.38 Ω
Insulation resistance	>8 GΩ
Max. current load in accordance with IEC 60364-5-523 by installation type	
Wall mounting	13 A
Installed in conduit or cable duct	11.5 A
Installed in cable tray	13.5 A
Environmental conditions	
Temperature	
Moving	-10 to 80°C
Static	-40 to 90°C
Mechanical characteristics	
Dimensions	
Length	25 m
Diameter	10.9 mm ±0.4 mm
Bend radius	
Single bend	>34 mm
Moving	≥85 mm
Drag chain data	
Acceleration	<60 m/s ²
Flex cycles ¹⁾	≥3,000,000
Speed	≤4 m/s
Weight	4.37 kg

Table 2: 8CM025.12-0 - Technical data

1) At an ambient temperature of 20°C and a flex radius of 125 mm.

4 Wiring

4.1 Motor cable construction

Pos.	Pieces	Name	Note
1	1	Motor lines	4x 0.75 mm ² + 2x 2x 0.35 mm ² 4x 1.5 mm ² + 2x 2x 0.75 mm ² 4x 4 mm ² + 2x 2x 1 mm ² 4x 10 mm ² + 2x 2x 1.5 mm ²
2	1	Male circular connector	BSTA 108 FR 19 58 0036 000 (for 8CMxxx.12-0, 8CMxxx.12-1) BSTA 108 FR 35 59 0036 000 (for 8CMxxx.12-3) CSTA 264 FR 48 25 0001 000 (for 8CMxxx.12-5)
3	1	Heat shrink tubing	
4	8	Wire end sleeves	

Table 3: Motor cable construction

4.2 8CMxxx.12-0, 8CMxxx.12-1, 8CMxxx.12-3


Male circular connector	Pin	Name	Function
	1	U	Motor connection U
	2	PE	Protective ground conductor
	3	W	Motor connection W
	4	V	Motor connection V
	A	T+	Temperature +
	B	T-	Temperature -
	C	B+	Brake +
	D	B-	Brake -

Table 4: Pinout - 8CMxxx.12-0, 8CMxxx.12-1, 8CMxxx.12-3 motor cables

4.3 8CMxxx.12-0




Figure 1: 8CMxxx.12-0 motor cables - Cable diagram