

# 8BCS0030.1111A-0

## 1 General information

- Can be used in cable drag chains
- Assembled specifically for use with ACOPOSmulti drive systems and B&R servo motors
- speedtec - Innovative connector system for secure connections

## 2 Order data

| Order number     | Short description                                                                                                                                                                                      | Figure                                                                              |
|------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| 8BCS0030.1111A-0 | ACOPOSmulti SinCos cable, length 30 m, 10x 0.14 mm <sup>2</sup> + 2x 0.5 mm <sup>2</sup> , SinCos 12-pin female speedtec connector, 15-pin male DSUB servo connector, can be used in cable drag chains |  |

Table 1: 8BCS0030.1111A-0 - Order data

## 3 Technical data

| Order number                               | 8BCS0030.1111A-0                                                                                                                  |
|--------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------|
| <b>General information</b>                 |                                                                                                                                   |
| Cable cross section                        | 5x 2x 0.14 mm <sup>2</sup> + 1x 2x 0.50 mm <sup>2</sup>                                                                           |
| Durability                                 | Oil resistance per VDE 0472 Part 803 as well as standard hydraulic oils <sup>1)</sup>                                             |
| Certifications                             |                                                                                                                                   |
| CE                                         | Yes                                                                                                                               |
| UKCA                                       | Yes                                                                                                                               |
| UL                                         | cULus E225616<br>Power conversion equipment                                                                                       |
| <b>Cable construction</b>                  |                                                                                                                                   |
| Supply lines                               |                                                                                                                                   |
| Quantity                                   | 2                                                                                                                                 |
| Wire insulation                            | Special thermoplastic material                                                                                                    |
| Wire colors                                | White/Green, white/red                                                                                                            |
| Variant                                    | Tinned copper stranded wire                                                                                                       |
| Cross section                              | 0.5 mm <sup>2</sup>                                                                                                               |
| Shield                                     | No                                                                                                                                |
| Stranding                                  | White/Red with white/green and filler elements                                                                                    |
| Signal line                                |                                                                                                                                   |
| Quantity                                   | 10                                                                                                                                |
| Wire insulation                            | Special thermoplastic material                                                                                                    |
| Wire colors                                | Blue, brown, yellow, gray, green, pink, red, black, violet, white                                                                 |
| Variant                                    | Tinned copper stranded wire                                                                                                       |
| Cross section                              | 0.14 mm <sup>2</sup>                                                                                                              |
| Shield                                     | No                                                                                                                                |
| Stranding                                  | Green with brown, gray with yellow, white with violet, black with red, pink with blue                                             |
| Cable stranding                            | With terminating foil shield                                                                                                      |
| Cable shield                               | Copper braiding, optical coverage >85% and foil shield                                                                            |
| Outer jacket                               |                                                                                                                                   |
| Material                                   | PUR                                                                                                                               |
| Color                                      | Green, similar to RAL 6018 flat                                                                                                   |
| <b>Connector</b>                           |                                                                                                                                   |
| Type                                       | 12-pin female speedtec SinCos connector                                                                                           |
| Mating cycles                              | <500                                                                                                                              |
| Contacts                                   | 12                                                                                                                                |
| Additional connectors                      | 15-pin male DSUB servo connector<br>Mating cycles: <200<br>Contacts: 15<br>Degree of protection per EN 60529: IP20 when connected |
| Degree of protection per EN 60529          | IP66/67 when connected                                                                                                            |
| <b>Electrical properties <sup>1)</sup></b> |                                                                                                                                   |
| Operating voltage                          | ≤30 V <sub>eff</sub>                                                                                                              |
| Test voltage                               |                                                                                                                                   |
| Wire - Wire                                | 1 kV                                                                                                                              |
| Wire - Shield                              | 0.8 kV                                                                                                                            |

Table 2: 8BCS0030.1111A-0 - Technical data

| Order number                        | 8BCS0030.1111A-0 |
|-------------------------------------|------------------|
| Conductor resistance                |                  |
| Supply lines                        | ≤40 Ω/km         |
| Signal line                         | ≤140 Ω/km        |
| Insulation resistance               | >200 MΩ*km       |
| Ambient conditions <sup>1)</sup>    |                  |
| Temperature                         |                  |
| Moving                              | -20°C to +80°C   |
| Static                              | -20°C to +90°C   |
| Mechanical properties <sup>1)</sup> |                  |
| Dimensions                          |                  |
| Length                              | 25 m             |
| Diameter                            | 7.85 mm ±0.2 mm  |
| Bend radius                         |                  |
| Single bend                         | ≥24 mm           |
| Moving                              | ≥60 mm           |
| Drag chain data                     |                  |
| Acceleration                        | ≤6 g             |
| Flex cycles <sup>2)</sup>           | >3,000,000       |
| Velocity                            | ≤4 m/s           |
| Weight                              | 2.51 kg          |

Table 2: 8BCS0030.1111A-0 - Technical data

- 1) Values refer to the raw cable being used.  
2) At an ambient temperature of 20°C and bend radius of 65 mm.

## 4 Wiring

### 4.1 Construction


|  |                                                       |                                                    |
|-------------------------------------------------------------------------------------|-------------------------------------------------------|----------------------------------------------------|
| Pos.                                                                                | Description                                           | Note                                               |
| 1                                                                                   | Encoder line                                          | 10x 0.14 mm <sup>2</sup> + 2x 0.50 mm <sup>2</sup> |
| 2                                                                                   | 12-pin female SinCos connector                        |                                                    |
| 3                                                                                   | DSUB housing 45°, metal plated, 15-pin male connector |                                                    |
| 4                                                                                   | Heat shrink tubing                                    |                                                    |

Table 3: 8BCS SinCos cables - Construction

### 4.2 Pinout



| Circular connector                                                                  | Pin | Description      | Function                  | Pin | DSUB connector                                                                        |
|-------------------------------------------------------------------------------------|-----|------------------|---------------------------|-----|---------------------------------------------------------------------------------------|
|  | 5   | A                | Channel A                 | 1   |  |
|                                                                                     | 10  | COM              | Encoder power supply 0 V  | 2   |                                                                                       |
|                                                                                     | 8   | B                | Channel B                 | 3   |                                                                                       |
|                                                                                     | 12  | +5 V out / 0.3 A | Encoder power supply +5 V | 4   |                                                                                       |
|                                                                                     | 4   | R\               | Reference pulse inverted  | 7   |                                                                                       |
|                                                                                     | 6   | A\               | Channel A inverted        | 9   |                                                                                       |
|                                                                                     | 11  | Sense COM        | Sense input 0 V           | 10  |                                                                                       |
|                                                                                     | 1   | B\               | Channel B inverted        | 11  |                                                                                       |
|                                                                                     | 2   | Sense +5 V       | Sense input +5 V          | 12  |                                                                                       |
|                                                                                     | 3   | R                | Reference pulse           | 14  |                                                                                       |

Table 4: 8BCS SinCos cables - Pinout

### 4.3 Cable diagram




Figure 1: 8BCS SinCos cables - Cable diagram