

8BCE0013.1111A-0

1 General information

- Can be used in cable drag chains
- Assembled specifically for use with ACOPOSmulti drive systems and B&R servo motors with Y-Tec connectors
- speedtec - Innovative connector system for secure connections

2 Order data

Order number	Short description	Figure
8BCE0013.1111A-0	EnDat 2.1 cables ACOPOSmulti EnDat 2.1 cable, length 13 m, 10x 0.14 mm ² + 2x 0.5 mm ² , 17-pin female speedtec EnDat connector, 15-pin male DSUB servo connector, can be used in cable drag chains	

Table 1: 8BCE0013.1111A-0 - Order data

3 Technical data

Order number	8BCE0013.1111A-0
General information	
Cable cross section	5x 2x 0.14 mm ² + 1x 2x 0.50 mm ²
Durability	Oil resistance per VDE 0472 Part 803 as well as standard hydraulic oils ¹⁾
Certifications	
CE	Yes
UKCA	Yes
UL	cULus E225616 Power conversion equipment
Cable construction	
Supply lines	
Quantity	2
Wire insulation	Special thermoplastic material
Wire colors	White/Green, white/red
Variant	Tinned copper stranded wire
Cross section	0.5 mm ²
Shield	No
Stranding	White/Red with white/green and filler elements
Signal line	
Quantity	10
Wire insulation	Special thermoplastic material
Wire colors	Blue, brown, yellow, gray, green, pink, red, black, violet, white
Variant	Tinned copper stranded wire
Cross section	0.14 mm ²
Shield	No
Stranding	Green with brown, gray with yellow, white with violet, black with red, pink with blue
Cable stranding	With terminating foil shield
Cable shield	Copper braiding, optical coverage >85% and foil shield
Outer jacket	
Material	PUR
Color	Green, similar to RAL 6018 flat
Connector	
Type	17-pin female speedtec EnDat connector
Mating cycles	<500
Contacts	17
Additional connectors	15-pin male DSUB servo connector Mating cycles: <200 Contacts: 15 Degree of protection per EN 60529: IP20 when connected
Degree of protection per EN 60529	IP66/67 when connected
Electrical properties ¹⁾	
Operating voltage	≤30 V _{eff}

Table 2: 8BCE0013.1111A-0 - Technical data

Order number	8BCE0013.1111A-0
Test voltage	
Wire - Wire	1 kV
Wire - Shield	0.8 kV
Conductor resistance	
Supply lines	≤40 Ω/km
Signal line	≤140 Ω/km
Insulation resistance	>200 MΩ*km
Ambient conditions ¹⁾	
Temperature	
Moving	-20°C to +80°C
Static	-20°C to +90°C
Mechanical properties ¹⁾	
Dimensions	
Length	13 m
Diameter	7.85 mm ±0.2 mm
Bend radius	
Single bend	≥24 mm
Moving	≥60 mm
Drag chain data	
Acceleration	≤6 g
Flex cycles ²⁾	>3,000,000
Velocity	≤4 m/s
Weight	1 kg

Table 2: 8BCE0013.1111A-0 - Technical data

- 1) Values refer to the raw cable being used.
2) At an ambient temperature of 20°C and bend radius of 65 mm.

4 Wiring

4.1 Construction


		
Pos.	Description	Note
1	Encoder cable	5x 2x 0.14 mm² + 2x 0.5 mm²
2	17-pin female circular connector	Dimensions: ø 26 x 58 mm
3	DSUB housing 45°, metal-plated, 15-pin	Dimensions: 31 x 15 x 40 mm
4	Heat shrink tubing	

Table 3: 8BCE EnDat 2.1 cables - Construction

4.2 Pinout



Circular connector	Pin	Description	Function	Pin	DSUB connector
	15	A	Channel A	1	
	10	COM (1, 3 - 9, 11, 13 - 15)	Encoder power supply 0 V	2	
	12	B	Channel B	3	
	7	+5 V out / 0.25 A	Encoder power supply +5 V	4	
	14	D	Data input	5	
	8	T	Clock output	8	
	16	A\	Channel A inverted	9	
	4	Sense COM	Sense input 0 V	10	
	13	B\	Channel B inverted	11	
	1	Sense +5 V	Sense input +5 V	12	
	17	D\	Data inverted	13	
	9	T\	Clock output inverted	15	

Table 4: 8BCE EnDat 2.1 cables - Pinout

4.3 Cable diagram




Figure 1: 8BCE EnDat 2.1 cables - Cable diagram