

8BCF0025.1231B-0

1 General information

- Can be used in cable drag chains
- Optimally assembled for use with servo motors with M12 encoder connector.

2 Order data

Order number	Short description	Figure
	EnDat 2.2 cables	
8BCF0025.1231B-0	EnDat 2.2 cable, length 25 m, 4x 0.14 mm ² + 4x 0.35 mm ² , 8-pin M12 circular connector, A-coded, 9-pin male DSUB connector, can be used in cable drag chains	

Table 1: 8BCF0025.1231B-0 - Order data

3 Technical data

Order number	8BCF0025.1231B-0
General information	
Cable cross section	4x 0.14 mm ² + 4x 0.35 mm ²
Durability	Oil resistance per DIN EN 50363-10-2 (VDE 0207-363-10-2) as well as standard cleaning agents and hydraulic oil ¹⁾
Certification	UL AWM Style 20963, 80°C, 30 V, E63216 ¹⁾
Certifications	
CE	Yes
UKCA	Yes
Cable construction	
Supply lines	
Quantity	4
Wire insulation	Special thermoplastic material
Wire colors	White/Green, brown/green, blue, white
Variant	Tinned copper stranded wire
Cross section	0.35 mm ²
Shield	No
Stranding	No
Signal line	
Quantity	4
Wire insulation	Polyolefin foam
Wire colors	Yellow, gray, pink, violet
Variant	Tinned copper stranded wire
Cross section	0.14 mm ²
Shield	No
Stranding	All 4 wires together
Cable stranding	With terminating foil shield
Cable shield	Copper/Tin braiding, optical coverage ≥85%
Outer jacket	
Material	PUR
Color	Green flat
Labeling	B&R 4x0,14 + 4x0,35 FLEX (UL) AWM STYLE 20963 80°C 30 V E63216 ¹⁾
Connector	
Type	8-pin female M12 circular connector, A-coded
Mating cycles	<500
Contacts	8
Additional connectors	9-pin male DSUB servo connector Mating cycles: <200 Contacts: 9 Degree of protection per EN 60529: IP20 when connected
Degree of protection per EN 60529	IP65/67 when connected
Electrical properties ¹⁾	
Operating voltage	≤30 V
Test voltage	
Wire - Wire	1 kV
Wire - Shield	0.5 kV

Table 2: 8BCF0025.1231B-0 - Technical data

Order number	8BCF0025.1231B-0
Conductor resistance	
Supply lines	≤55 Ω/km
Signal line	≤134 Ω/km
Insulation resistance	>200 MΩ*km
Ambient conditions ¹⁾	
Temperature	
Moving	-40°C to +80°C
Static	-40°C to +80°C
Mechanical properties ¹⁾	
Dimensions	
Length	25 m
Diameter	6 mm ±0.2 mm
Bend radius	
Single bend	≥19 mm
Moving	≥47 mm
Drag chain data	
Acceleration	≤6 g
Flex cycles ²⁾	≥3000000
Velocity	≤4 m/s
Weight	1.5 kg

Table 2: 8BCF0025.1231B-0 - Technical data

- 1) Values refer to the raw cable being used.
2) Valid at an ambient temperature of 20°C and bend radius of 78 mm.

4 Wiring

4.1 Cable construction


		
Pos.	Description	Note
1	Encoder line	4 x 0.14 + 4 x 0.35 mm ²
2	8-pin circular connector, A-coded Contact connector	It must be possible to establish a shield connection over a wide area. Dimensions: ø 19 x 43 mm
3	Heat shrink tubing	
4	DSUB housing 45°, metal plated, 9-pin connector Contact pins	Dimensions: 31 x 15 x 40 mm

Table 3: 8BCFxxxx.1231B-0 - Cable construction

4.2 Pinout



Circular connector	Pin	Description	Function	Pin	DSUB connector
	8	+12 V out	Encoder power supply +12 V	1	
	3	D	Data input	4	
	4	D\	Data inverted	8	
	7	T	Clock output	5	
	6	T\	Clock output inverted	9	
	1	Batt COM	Battery buffer 0 V	7	
	5	COM	Encoder power supply 0 V	6	
		---	Coding contact		
	2	VBatt	Backup battery power supply	2	

Table 4: 8BCFxxxx.1231B-0 - Pinout

4.3 Cable diagram




Figure 1: 8BCFxxxx.1231B-0 - Cable diagram