


### 3.2 Keypad Module 16 Keys



| Technical Data   |  |
|--|--|
| <b>Model Number</b>  | 4E0011.01-090  |
| <b>Number of Keys</b>  | 16 short stroke keys   |
| <b>Number of LEDs</b>  | 16 (yellow)  |
| <b>Labeling</b>  | Can be labeled by the user   |
| <b>Temperature Range</b><br><b>Operating</b><br><b>Storage</b> | 0 to 50 °C (32 to 122 °F)<br>-20 to 60 °C (-4 to 140 °F)   |
| <b>Relative Humidity</b><br><b>Operating</b><br><b>Storage</b> | 5 to 95 % (non-condensing)<br>5 to 95 % (non-condensing)   |
| <b>Shock</b>   | Conforms to IEC 60068-2-27<br>15g equivalent, 150 m/sec <sup>2</sup> , 11 msec, 3 axes (positive and negative)           |
| <b>Vibration</b>   | Conforms to IEC 60068-2-6<br>1g equivalent, 10-58 Hz; 0.075 mm<br>58-150 Hz; 9.8m/sec <sup>2</sup><br>20 cycles per axis |
| <b>Current Requirements</b>                                    | 1.5 mA at 24 VDC (each LED requires an additional 3 mA when lit)   |