


8GA50-120

Technical data



8GA50-120hh003klmm

8GA50-120hh004klmm

8GA50-120hh005klmm

8GA50-120hh008klmm

8GA50-120hh010klmm

8GA50-120hh009klmm

8GA50-120hh012klmm

8GA50-120hh015klmm

8GA50-120hh016klmm

8GA50-120hh020klmm

8GA50-120hh025klmm

8GA50-120hh032klmm

8GA50-120hh040klmm

8GA50-120hh064klmm

8GA50-120hh100klmm

Gearboxes

Number of stages			1			2									
Ratio i	3	4	5	8	10	9	12	15	16	20	25	32	40	64	100
Nominal output torque T _{2N} [Nm] ¹⁾	80	105	130	120	95	157	195	172	195		172	195	172	120	95
Max. output torque T _{2max} [Nm] ¹⁾	128	168	208	192	152	251.2	312	275.2	312		275.2	312	275.2	192	152
Emergency stop torque T _{2estop} [Nm] ²⁾	160	210	260	240	190	314	390	344	390		344	390	344	240	190
No load running torque at 20°C and 3,000 [min ⁻¹] [Nm]	1	0.9	0.8	0.7	0.6							0.5			
Max. average input speed at 50% T _{2N} and S1 n _{1N50%} [min ⁻¹]	2500		2600	3000											
Max. average input speed at 100% T _{2N} and S1 n _{1N100%} [min ⁻¹]	1900			2700	3000	2100	2200	2600	2500	2800	3000				
Max. input speed n _{1max} [min ⁻¹]	6500														
Max. backlash j _{lt} [arcmin]	<12					<16									
Reduced backlash j _{lt} [arcmin]						-									
Torsional rigidity C _{t21} [Nm/arcmin]	10					13									
Tilting rigidity C _{2K} [Nm/arcmin]						-									
Max. tilting moment M _{2KMax} [Nm]						-									
Max. radial force for 30,000 h Fr _{max} [N] ³⁾						2150									
Max. radial force for 20,000 h Fr _{max} [N] ³⁾						2500									
Max. axial force for 30,000 h Fa _{max} [N] ³⁾						3000									
Max. axial force for 20,000 h Fa _{max} [N] ³⁾						4000									
Running noise L _{PA} [dB(A)] ⁴⁾						75									
Efficiency at full load η [%]	94					92									
Min. operating temperature B _{Tempmin} [°C] ⁵⁾						-25									
Max. operating temperature B _{Tempmax} [°C] ⁵⁾						90									
Mounting orientation						Any									
Protection class						IP 54									
Weight m [Kg]	13.5					15.7									
Moment of inertia J ₁ [Kgcmm ²]	2.87	1.92	1.6	1.35	1.3	2.65	2.57	2.54	1.76	1.5		1.3			

¹⁾ The entries refer to an output shaft speed of $n_2=100\text{min}^{-1}$ and application factor $K_A=1$ as well as S1 operating mode for electrical machines and $T=30^\circ\text{C}$; depending on the respective motor shaft diameter


²⁾ Approved for 1000x

³⁾ With reference to the middle of the output shaft; the entries refer to an output shaft speed of $n_2=100\text{min}^{-1}$ and application factor $K_A=1$ as well as S1 operating mode for electrical machines and $T=30^\circ\text{C}$


⁴⁾ Noise level at a distance of 1 m; measured at a drive speed of $n_1=3000\text{min}^{-1}$ without a load; $i=5$

⁵⁾ With reference to the middle of the housing surface

1 stage gearboxes



2 stage gearboxes



Alternative output shaft options

Smooth shaft

