PPC2200 - AP9x3|AP1000 - Cabinet-mounted
Device number key

2. Version	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18
	Group		Automation Panel		Free	Free	Free	Free	Panel version	CPU / RAM	CFast slot	IF Option	Operating system	Real time operating system			Version (000 = standard)	
PPC2200	5	Q			0	0	0	0							-	0	0	0
Automation Panel cabinet mounted 7.0" (768x480), single-touch RES (5AP1120.0702-000)			2	A														
Automation Panel cabinet mounted 7.0" (768x480), multi-touch PCT (5AP1130.0702-000)			2	B														
Automation Panel cabinet mounted 5.7" (640x480), single-touch RES (5AP1120.0573-000)			3	A														
Automation Panel cabinet mounted 5.7" (640x480), single-touch RES, keys (5AP1151.0573-000)			3	B														
Automation Panel cabinet mounted 10.4" (640x480), single-touch RES (5AP1120.1043-000)			3	C														
Automation Panel cabinet mounted 10.4" (640x480), single-touch RES, 22 function keys (5AP1180.1043-000)			3	D														
Automation Panel cabinet mounted 10.4" (640x480), single-touch RES, 38 function keys and 20 system keys (5AP1181.1043-000)			3	E														
Automation Panel cabinet mounted 10.4" (640x480), single-touch RES, 44 function keys and 20 system keys (5AP1182.1043-000)			3	F														
Automation Panel cabinet mounted 12.4" (800x600), single-touch RES (5AP1120.1214-000)			4	A														
Automation Panel cabinet mounted 12,1" (1024x768), single-touch RES (5AP923.1215-00)			5	A														
Automation Panel cabinet mounted 15.0" (1024x768), single-touch RES (5AP923.1505-00)			5	B														
Automation Panel cabinet mounted 15.0" (1024x768), single-touch RES (5AP1120.1505-000)			5	C														
Automation Panel cabinet mounted 15.0" (1024x768), single-touch RES, keys (5AP1180.1505-000)			5	D														
Automation Panel cabinet mounted 15.0" (1024x768), single-touch RES, 32 function keys and 92 system keys (5AP1181.1505-000)			5	E														
Automation Panel cabinet mounted 19.0" (1280x1024), single-touch RES (5AP923.1906-00)			6	A														
Automation Panel cabinet mounted 19.0" (1280x1024), single-touch RES (5AP1120.1906-000)			6	B														
Automation Panel cabinet mounted 15.6" (1366x768), multi-touch PCT (5AP933.156B-00)			B	A														
Automation Panel cabinet mounted 18.5" (1366x768), multi-touch PCT (5AP933.185B-00)			B	B														
Automation Panel cabinet mounted 15.6" (1366x768), single-touch RES (5AP1120.156B-000)			B	C														
Automation Panel cabinet mounted 21.5" (1920x1080), multi-touch PCT (5AP933.215C-00)			C	A														
Automation Panel cabinet mounted 24.0" (1920x1080), multi-touch PCT (5AP933.240C-00)			C	B														
Automation Panel cabinet mounted 18.5" (1920x1080), multi-touch PCT (5AP1130.185C-000)			C	C														
Automation Panel cabinet mounted 15.6" (1920x1080), multi-touch PCT (5AP1130.156C-000)			C	D														
Automation Panel cabinet mounted 10.1" (1280x800), single-touch RES (5AP1120.101E-000)			E	A														
Automation Panel cabinet mounted 12.1" (1280x800), single-touch RES (5AP1120.121E-000)			E	B														
Automation Panel cabinet mounted 10.1" (1280x800), multi-touch PCT (5AP1130.101E-000)			E	C														
Automation Panel cabinet mounted 12.1" (1280x800), multi-touch PCT (5AP1130.121E-000)			E	D														
Automation Panel cabinet mounted 7.0" (768x480), single-touch RES (5AP1120.0702-I00)			2	A					I									
Automation Panel cabinet mounted 10.4" (640x480), single-touch RES, RFID (5AP1125.1043-I00)			3	A					I									
Automation Panel cabinet mounted 10.4" (800x600), single-touch RES, RFID (5AP1125.1044-I00)			4	A					I									
Automation Panel cabinet mounted 15.0" (1024x768), single-touch RES, RFID (5AP1125.1505-I00)			5	A					I									
Automation Panel cabinet mounted 12.1" (1024x768), single-touch RES (5AP923.1215-I00)			5	B					I									
Automation Panel cabinet mounted 15.0" (1024x768), single-touch RES (5AP923.1505-I00)			5	C					I									
Automation Panel cabinet mounted 15.0" (1024x768), single-touch RES (5AP923.1505-I01)			5	D					I									
Standard									0									
Full customized (incl. mylar versions type "I")									C									
Mylar version									F									
Industry specific									I									
Intel Atom E3930 1.3 GHz, Dual-Core, 2GB (5PPC2200.AL02-000)										1								
Intel Atom E3930 1.3 GHz, Dual-Core, 4GB (5PPC2200.AL04-000)										2								
Intel Atom E3940 1.6 GHz, Quad-Core, 4GB (5PPC2200.AL14-000)										3								
Intel Atom E3940 1.6 GHz, Quad-Core, 8GB (5PPC2200.AL18-000)										4								
Without											0							
CFast 2 GB SLC (5CFAST.2048-00)											1							
CFast 4 GB SLC (5CFAST.4096-00)											2							
CFast 8 GB SLC (5CFAST.8192-00)											3							
CFast 16 GB SLC (5CFAST.016G-00)											4							
CFast 32 GB SLC (5CFAST.032G-00)											5							
CFast 32 GB MLC (5CFAST.032G-10)											A							
CFast 64 GB MLC (5CFAST.064G-10)											B							
CFast 128 GB MLC (5CFAST.128G-10)											C							
CFast 256 GB MLC (5CFAST.256G-10)											D							
Without												0						
Powerlink, FRAM, CAN, RS232 (5ACCIF01.FPSC-000)												1						
Powerlink, FRAM, RS232 full (5ACCIF01.FPLS-000)												2						
Powerlink, nvSRAM, CAN, RS232, X2X (5ACCIF01.FPSC-001)												3						
Powerlink, nvSRAM, RS232 full (5ACCIF01.FPLS-001)												4						
CAN 82527 (5ACCIF01.ICAN-000)												5						
2x Powerlink, nvSRAM (5ACCIF01.FPLK-000)												6						
Powerlink, nvSRAM, 2x CAN, X2X (5ACCIF01.FPCC-000)												7						
Powerlink, FRAM, CAN, RS485 (5ACCIF01.FPCS-000)												8						
2x RS422/485 (5ACCIF01.FSS0-000)												9						
2xETH 10/100/1000 (5ACCIF03.CETH-000)												W						
Without													0					
B&R Linux 9 64-Bit, UEFI Boot (pre-installed) (5SWLIN.0745-MUL)													K					
Windows 10 IoT Entry 2016 64-Bit, UEFI Boot (pre-installed) (5SWW10.0545-MUL)													L					
Windows 10 IoT Entry 2016 64-Bit, Legacy BIOS Boot (pre-installed) (5SWW10.0559-MUL)													N					
B&R Linux 9 64-Bit, Legacy BIOS Boot (pre-installed) (5SWLIN.0759-MUL)													P					
Without														0				
Automation Runtime Embedded TG license (MSD) (TG is plugged on interface USB 2) (1TG4601.06-5 & 0TG1000.01)														2				
Automation Runtime Embedded Terminal TG (MSD) (TG is plugged on interface USB 2) (1TG4601.06-T & 0TG1000.01)														3				
Automation Runtime Embedded TG license (HID) (TG is plugged on interface USB 2) (1TG4601.06-5 & 0TG1000.02)														7				
Automation Runtime Embedded Terminal TG (HID) (TG is plugged on interface USB 2) (1TG4601.06-T & 0TG1000.02)														8				
Automation Runtime Simulation TG license (MSD) (TG is plugged on interface USB 2) (1TG4600.00 & 0TG1000.01)														9				
Automation Runtime Simulation TG license (HID) (TG is plugged on interface USB 2) (1TG4600.00 & 0TG1000.02)														A				