8BCM0020.15250-0

1 General information

- Can be used in cable drag chains
- Assembled specifically for motor cables 8BCMxxxx.1523A-0 with standard size 1.5 connector
- speedtec - Innovative connector system for secure connections

2 Order data

Model number	Short description	Figure
	Motor cables 10 mm²	
8BCM0020.15250-0	Cable extension for 10 mm² motor cables with speedtec/standard connector size 1.5, length 20 m, can be used in cable drag chains	

Table 1: 8BCM0020.15250-0 - Order data

3 Technical data

Model number	8BCM0020.15250-0
General information	
Cable cross section	4x 10 mm² + (2x 0.75 mm²)C + (2x 1.5 mm²)C
Durability	Oil resistance per HD 22.10 appendix A DIN EN 60811-404 [1]
Certification	E170315 cRUus AWM STYLE 21223 AWM I/II A/B 80°C 1000 V FT1 [1]
Certifications	
CE	Yes
UL	cULus E225616 Power conversion equipment
EAC	Yes
Cable construction	
Power lines	
Quantity	4
Wire insulation	PP
Wire colors	Black, brown, blue, yellow/green
Variant	Tinned copper stranded wire
Cross section	10 mm²
Shield	No
Stranding	No
Signal line	
Quantity	4
Wire insulation	PP
Wire colors	White, white/red, white/blue, white/green
Variant	Tinned copper stranded wire
Cross section	2x 0.75 mm² + 2x 1.5 mm²
Shield	Separate shielding for pairs, tinned copper braiding, optical coverage >85% and foil shield
Stranding	White with white/red and white/blue with white/green
Cable stranding	With filler elements and foil shield
Cable shield	Tinned copper braiding, optical coverage >85% and foil shield
Outer jacket	
Material	TPU
Color	Orange, similar to RAL 2003 flat
Labeling	B&R 4 G 10 + (2x0.75)C + (2x1.5)C C E170315 cRU-us AWM STYLE 21223 AWM I/II A/B 80°C 1000 V FT1 [1]
Connector	
Type	8-pin female speedtec motor connector, size 1.5
Mating cycles	<500
Contacts	8 (4 power and 4 signal contacts)
Additional connectors	8-pin male coupling Connection cycles: <500 Contacts: 8 Degree of protection per EN 60529: IP66/67 when connected
Degree of protection per EN 60529	IP66/67 when connected
Electrical properties [1]	
Operating voltage	Max. 1000 V AC (UL)

Table 2: 8BCM0020.15250-0 - Technical data

Model number	8BCM0020.15250-0
Test voltage	
Wire - Wire	4 kV
Wire - Shield	4 kV
Conductor resistance	
Power lines	≤2 Ω/km
Signal line	0.75 mm²: ≤26.7 Ω/km, 1.5 mm²: ≤13.7 Ω/km
Insulation resistance	≥500 MΩ*km
Current-carrying capacity per DIN VDE 0298 part 4, table 11	
Wall mounting	64.6 A
Installed in conduit or cable duct	54.6 A
Installed in cable tray	68.3 A
Ambient conditions [1]	
Temperature	
Moving	-20°C to +80°C
Static	-20°C to +90°C
Mechanical properties [1]	
Dimensions	
Length	20 m
Diameter	20.1 mm ± 0.4 mm
Bend radius	
Single bend	>62 mm
Moving	>154 mm
Drag chain data	
Acceleration	Max. 50 m/s² (depends on the length of the travel path)
Flex cycles [2]	≥5,000,000
Velocity	Max. 300 m/min
Weight	10.8 kg


Table 2: 8BCM0020.15250-0 - Technical data

1) Values refer to the raw cable being used.
2) At an ambient temperature from -20°C to +60°C.

4 Wiring

4.1 Cable construction

Construction



Pos.	Description	Note
1	Motor line	4x 10 mm² + 2x 0.75 mm² + 2x 1.5 mm²
2	8-pin female circular connector	
3	8-pin male coupling	

Table 3: 10 mm² motor cables - Cable construction

4.2 Pinout



Circular connector	Pin	Description	Function	Coupling
	U	U	Motor connection U	
	Ground symbol	PE	Protective ground conductor	
	W	W	Motor connection W	
	V	V	Motor connection V	
	1	T+	Temperature +	
	2	T-	Temperature -	
	+	B+	Brake +	
	-	B-	Brake -	

Table 4: Pinout

4.3 Cable diagram




Figure 1: 8BCMxxxx.15250-0 - Cable diagram