

8BCM0007.15250-0

1 General information

- Can be used in cable drag chains
- Assembled specifically for motor cables 8BCMxxxx.1523A-0 with standard size 1.5 connector
- speedtec - Innovative connector system for secure connections

2 Order data

Model number	Short description	Figure
8BCM0007.15250-0	Motor cables 10 mm² Cable extension for 10 mm ² motor cables with speedtec or standard connector, size 1.5, length 7 m, can be used in cable drag chains	

Table 1: 8BCM0007.15250-0 - Order data

3 Technical data

Model number	8BCM0007.15250-0
General information	
Cable cross section	4x 10 mm ² + (2x 0.75 mm ²)C + (2x 1.5 mm ²)C
Durability	Oil resistance per HD 22.10 appendix A DIN EN 60811-404 ¹⁾
Certification	E170315 cRUus AWM STYLE 21223 AWM I/II A/B 80°C 1000 V FT1 ¹⁾
Certifications	
CE	Yes
UL	cULus E225616 Power conversion equipment
Cable construction	
Power lines	
Quantity	4
Wire insulation	PP
Wire colors	Black, brown, blue, yellow/green
Variant	Tinned copper stranded wire
Cross section	10 mm ²
Shield	No
Stranding	No
Signal line	
Quantity	4
Wire insulation	PP
Wire colors	White, white/red, white/blue, white/green
Variant	Tinned copper stranded wire
Cross section	2x 0.75 mm ² + 2x 1.5 mm ²
Shield	Separate shielding for pairs, tinned copper braiding, optical coverage >85% and foil shield
Stranding	White with white/red and white/blue with white/green
Cable stranding	With filler elements and foil shield
Cable shield	Tinned copper braiding, optical coverage >85% and foil shield
Outer jacket	
Material	TPU
Color	Orange, similar to RAL 2003 flat
Labeling	B&R 4 G 10 + (2x0.75)C + (2x1.5)C C E170315 cRU-us AWM STYLE 21223 AWM I/II A/B 80°C 1000 V FT1 ¹⁾
Connector	
Type	8-pin female speedtec motor connector, size 1.5
Mating cycles	<500
Contacts	8 (4 power and 4 signal contacts)
Additional connectors	8-pin male coupling Connection cycles: <500 Contacts: 8 Degree of protection per EN 60529: IP66/67 when connected
Degree of protection per EN 60529	IP66/67 when connected
Electrical properties ¹⁾	
Operating voltage	Max. 1000 V AC (UL)

Table 2: 8BCM0007.15250-0 - Technical data

Model number	8BCM0007.15250-0
Test voltage	
Wire/Wire	4 kV
Wire/Shield	4 kV
Conductor resistance	
Power lines	$\leq 2 \text{ } \Omega/\text{km}$
Signal line	$0.75 \text{ mm}^2: \leq 26.7 \text{ } \Omega/\text{km}, 1.5 \text{ mm}^2: \leq 13.7 \text{ } \Omega/\text{km}$
Insulation resistance	$\geq 500 \text{ M}\Omega \cdot \text{km}$
Current-carrying capacity per DIN VDE 0298 part 4, table 11	
Wall mounting	64.6 A
Installed in conduit or cable duct	54.6 A
Installed in cable tray	68.3 A
Ambient conditions ¹⁾	
Temperature	
Moving	-20°C to +80°C
Static	-20°C to +90°C
Mechanical properties ¹⁾	
Dimensions	
Length	7 m
Diameter	$20.1 \text{ mm} \pm 0.4 \text{ mm}$
Bend radius	
Single bend	>62 mm
Moving	>154 mm
Drag chain data	
Acceleration	Max. 50 m/s^2 (depends on the length of the travel path)
Flex cycles ²⁾	$\geq 5,000,000$
Velocity	Max. 300 m/min
Weight	3.8 kg

Table 2: 8BCM0007.15250-0 - Technical data

1) Values refer to the raw cable being used.

2) At an ambient temperature from -20°C to +60°C.

4 Wiring

4.1 Cable construction

Construction


		
Pos.	Description	Note
1	Motor line	$4 \times 10 \text{ mm}^2 + 2 \times 0.75 \text{ mm}^2 + 2 \times 1.5 \text{ mm}^2$
2	8-pin female circular connector	
3	8-pin male coupling	

Table 3: 10 mm^2 motor cables - Cable construction

4.2 Pinout



Circular connector	Pin	Description	Function	Coupling
	U	U	Motor connection U	
	Ground symbol	PE	Protective ground conductor	
	W	W	Motor connection W	
	V	V	Motor connection V	
	1	T+	Temperature +	
	2	T-	Temperature -	
	+	B+	Brake +	
	-	B-	Brake -	

Table 4: Pinout

4.3 Cable diagram




Figure 1: 8BCMxxxx.15250-0 - Cable diagram