







Nennmaßbereich	Allgemeintoleranz nach DIN ISO 2768 mittel
bis 6 mm	± 0,1 mm
über 6 bis 30 mm	± 0,2 mm
über 30 bis 120 mm	± 0,3 mm
über 120 bis 400 mm	± 0,5 mm
über 400 bis 1000 mm	± 0,8 mm



Ausschnittmaße 199 ± 0,5 mm x 143 ± 0,5 mm passend für

- 4PP320.0571-01
- 4PP320.0571-35
- 4PP420.0571-45
- 4PP420.0571-65
- 4PP420.0571-75
- 4PP420.0571-A5
- 4PP420.0571-B5
- 4PP420.0573-75
- 5PP320.0571-29
- 5PP320.0571-39
- 5PP320.0573-39
- 5PP320.0573-3B

								Maßstab / scale		Oberfl.Behandlung / surface treatment	
						Werkstoff, Halbzeug / material, half-finished items					
.		.		.		.		Benennung / designation			
.		.		.		Bearbeiter designer		Datum / Date		Name	
.		.		.		Gepuëft approved		22.04.2008		RAM	
.		.		.				.		.	
.		.		.							
.		.		.							
.		.		.							
.		.		.				Bernecker & Rainer		Materialnummer - Revision / material number - revision	
.		.		.		A - 5142 Eggelsberg				Blatt / sheet	
.		.		.						Bl. /sh.	
Rev.	Aenderung / changes	Datum / Date	Name	Ursprung original	.	Werkstueckkante / edge of workpieces DIN ISO 13715 (DIN 6784)			Format: A3 Querformat		