

X20(c)HB2881

1 General information

The POWERLINK bus controller X20BC8083 and the stand-alone hubs X20HB8880 and X20HB8815 are equipped with a modular hub expansion. An additional 1 or 2 slots are available, depending on the bus base used. The X20HB2881 hub expansion module can be operated in these slots. Note that the hardware revision of the X20BC8083 and the X20HB8880 must be $\geq F0$.

The hub expansion module is a 2x hub. The Ethernet connection is made using 62.5/125 μm or 50/125 μm fiber optic multimode cable with a duplex LC connection. The status of the module and network are indicated by LEDs.

- Hub expansion module
- 2x Hub 100 BASE-FX

Information:

This module is not suitable for POWERLINK ring redundancy applications.

2 Coated modules

Coated modules are X20 modules with a protective coating for the electronics component. This coating protects X20c modules from condensation and corrosive gases.

The modules' electronics are fully compatible with the corresponding X20 modules.

For simplification purposes, only images and module IDs of uncoated modules are used in this data sheet.

The coating has been certified according to the following standards:

- Condensation: BMW GS 95011-4, 2x 1 cycle
- Corrosive gas: EN 60068-2-60, method 4, exposure 21 days



3 Order data

Model number	Short description	Figure
	System modules for the X20 hub system	
X20HB2881	X20 hub expansion module, integrated 2-port hub, for fiber optic cable	
X20cHB2881	X20 hub expansion module, coated, integrated 2-port hub, for fiber optic cable	

Table 1: X20HB2881, X20cHB2881 - Order data

4 Technical data

Model number	X20HB2881		X20cHB2881
Short description			
Hub	2 Fast Ethernet interfaces for fiber optic cable for hub expansion		
General information			
Status indicators	Module status, bus function		
Diagnostics			
Module status	Yes, using status LED		
Bus function	Yes, using status LED		
Power consumption	2.3 W (Rev. <E0: 2.8 W)	2.3 W	
Additional power dissipation caused by actuators (resistive) [W]	-		
Certifications			
CE	Yes		
ATEX	Zone 2, II 3G Ex nA nC IIA T5 Gc IP20, Ta (see X20 user's manual) FTZÜ 09 ATEX 0083X		
UL	cULus E115267 Industrial control equipment		
HazLoc	cCSAus 244665 Process control equipment for hazardous locations Class I, Division 2, Groups ABCD, T5		
EAC	Yes		
KC	Yes	-	
Interfaces			
Type	Hub expansion module		
Variant	2x duplex LC female		
Transfer rate	100 Mbit/s		
Transfer			
Physical layer	100BASE-FX		
Half-duplex	Yes		
Full-duplex	No		
Autonegotiation	No		
Auto-MDI/MDIX	No		
Hub propagation delay	0.96 to 1 µs		
Wave length	Typ. 1300 nm Rx range: 1270 to 1380 nm Tx range: 1270 to 1380 nm		
Cable fiber type	Multimode fiber with 62.5/125 µm or 50/125 µm core diameter On both sides: Duplex LC male connector		
Optical power budget			
Glass fiber 62.5/125 µm, NA = 0.275	11 dB		
Glass fiber 50/125 µm, NA = 0.200	7.5 dB		
Cable length			
Half-duplex	Max. 175 m between 2 stations (segment length)		
POWERLINK	Max. 2 km between 2 stations (segment length)		
Electrical properties			
Electrical isolation	Power supply isolated from Ethernet (IF1 and IF2)		
Operating conditions			
Mounting orientation			
Horizontal	Yes		
Vertical	Yes		
Installation elevation above sea level			
0 to 2000 m	No limitations		
>2000 m	Reduction of ambient temperature by 0.5°C per 100 m		
Degree of protection per EN 60529	IP20		
Ambient conditions			
Temperature			
Operation			
Horizontal mounting orientation (with 1 hub)	-25 to 55°C (Rev. <E0: 0 to 45°C)	-25 to 55°C	
Horizontal mounting orientation (with ≥2 hubs)	-25 to 50°C (Rev. <E0: 0 to 40°C)	-25 to 50°C	
Vertical mounting orientation (with 1 hub)	-25 to 40°C (Rev. <E0: 0 to 40°C)	-25 to 40°C	
Vertical mounting orientation (with ≥2 hubs)	-25 to 35°C (Rev. <E0: 0 to 35°C)	-25 to 35°C	
Derating	-		
Storage	-40 to 85°C		
Transport	-40 to 85°C		


Table 2: X20HB2881, X20cHB2881 - Technical data

Model number	X20HB2881	X20cHB2881
Relative humidity		
Operation	5 to 95%, non-condensing	Up to 100%, condensing
Storage	5 to 95%, non-condensing	
Transport	5 to 95%, non-condensing	
Mechanical properties		
Slot	Hub expansion for X20BC8083 and X20HB8880 ¹⁾	Hub expansion for X20cBC8083 and X20cHB8880 ²⁾

Table 2: X20HB2881, X20cHB2881 - Technical data

- 1) The hardware revision of X20BC8083 and X20HB8880 must be ≥F0.
2) The hardware revision of X20cBC8083 and X20cHB8880 must be ≥F0.

5 Operating and connection elements



5.1 LED status indicators

Figure	LED	Color	Status	Description
	ERR	Red	On	Slot not detected
	RDY	Orange	On	Slot detected, module is active
	L/A IFx	Green	On	A link to the remote station has been established.
			Blinking	A link to the remote station has been established. Indicates Ethernet activity is taking place on the bus.

5.2 Ethernet interfaces

Figure	Description
<p>Duplex LC (IF1) Tx Rx Duplex LC (IF2) Tx Rx</p>	100 BASE-FX, Duplex LC female

5.2.1 Wiring guidelines for X20 modules with fiber optic cable

The following wiring guidelines must be observed:

- Cable fiber type: Multimode fiber with 62.5/125 µm or 50/125 µm core diameter
- On both sides: Duplex LC male connector
- Observe minimum cable flex radius (see data sheet for the cable)

6 Network size and collision detection


Information:

This section applies to the use of Ethernet networks, not POWERLINK networks.

According to Ethernet specification IEEE 802.3, the transmission duration of a frame of minimum length must always be greater than the round-trip delay time (RTD). RTD is the time needed by a data packet to travel from one end of the network to the other.

If this is not observed, collision detection can no longer be guaranteed.

Illustration of RTD



When using fiber optic cables, the default maximum size is 175 m. Since there are often different devices in a network using different PHYs, the propagation delay of the frames changes since each PHY has different latency. This also affects the network size, and collision detection can no longer be guaranteed at 175 m.

For this reason, it is necessary to re-check whether the transmission duration of a frame of minimum length is actually greater than the maximum RTD.

Example for calculating network size

- Transfer rate: 100 Mbit/s
- Length of the fiber optic cable: 175 m
- Number of hubs: 2
- Hub propagation delay of a frame: 1 μ s
- Minimum frame size in the Ethernet network: 72 bytes

Calculation procedure

1. How long does 1 byte need at 100 Mbit/s – 100 Mbit/s / 8 = 12.5 MB/s	$\frac{12,500,000}{1} = \frac{1}{x}$ $x = \frac{1s}{12,500,000} = 80ns$
2. Propagation delay of minimum Ethernet frame – Minimum frame in Ethernet network: 72 bytes	$72 * 80ns = 5.76\mu s$
3. Propagation delay in cable and hub (100 m cable = 0.5 μ s) – 175 m cable = 1.75 x 0.5 μ s – 2 hubs = 2 x 1 μ s	$\frac{175}{100}m * 0.5\mu s + 2\mu s = 2.875\mu s$
4. Calculation of total propagation delay – Outbound/Inbound propagation delay	$2.875\mu s * 2 = 5.75\mu s$

Result

Collision detection is possible since the total time of 5.75 μ s is less than the minimum Ethernet propagation delay of 5.76 μ s.

With a longer cable or device with different latency, collision detection would no longer exist.