

X20TB06/X20TB12

1 General information

The X20 24 VDC modules are wired using the X20TB06 and X20TB12 terminal blocks.

- Tool-free wiring with push-in technology
- Simple wire release using lever
- Ability to label each terminal
- Plain text labeling also possible
- Test access for standard probes
- Can be customer-coded

2 Order data


	
	<div>X20TB06X20TB12</div>
Model number	Short description
	Terminal blocks
X20TB06	X20 terminal block, 6-pin, 24 VDC keyed
X20TB12	X20 terminal block, 12-pin, 24 VDC keyed

Table 1: X20TB06, X20TB12 - Order data

3 Technical data

Model number	X20TB06	X20TB12
General information		
Certifications		
CE	Yes	
ATEX	Zone 2, II 3G Ex nA nC IIA T5 Gc IP20, Ta (see X20 user's manual) FTZÚ 09 ATEX 0083X	
UL	cULus E115267 Industrial control equipment	
DNV GL	Temperature: B (0 - 55°C) Humidity: B (up to 100%) Vibration: B (4 g) EMC: B (bridge and open deck)	
LR	ENV1	
KR	Yes	
ABS	Yes	
Terminal block		
Number of pins	6	12
Type of terminal block	Push-in terminal	
Push-in force per contact	Typ. 10 N	
Cable type	Only copper wires (no aluminum wires!)	
Wire stripping length	7 to 9 mm	
Connection cross section		
Solid wires	0.08 to 2.50 mm² / 28 to 14 AWG	
Fine-stranded wires	0.25 to 2.50 mm² / 24 to 14 AWG	
With wire end sleeves	0.25 to 1.50 mm² / 24 to 16 AWG	
With double wire end sleeves	Up to 2x 0.75 mm²	
Distance between contacts		
Left - Right	4.2 mm	
Above - Below	10.96 mm	
Electrical properties		
Nominal voltage	240 VAC / 48 VDC	
Max. voltage	300 VAC / 60 VDC	
Nominal current ¹⁾	10 A / contact	
Contact resistance	≤5 mΩ	
Ambient conditions ²⁾		
Temperature		
Operation	Corresponds to the X20 module used	
Relative humidity		
Operation	Corresponds to the X20 module used	

Table 2: X20TB06, X20TB12 - Technical data

- 1) Take the respective limit data for the I/O modules into consideration!
 2) Identical for operation, storage and transport.


Warning!

It is possible to come into contact with parts that carry voltage when the terminal block is disconnected. For this reason, working on a disconnected terminal block is not permitted at voltages starting at 50 V.

4 Unique terminal numbering

Each terminal connection is unique and can be identified by the numbers in the plastic. In this way, terminal assignments can be clearly assigned in the planning stage without any danger of mix-up.

- Upper number: Row number 1 or 2
- Lower number: Terminal numbers 1 to 3 (6-pin terminal block), 1 to 6 (12-pin terminal block), 1 to 8 (16-pin terminal block)



5 Wiring

In order to achieve a secure connection in the terminal blocks, wires must be stripped accordingly.




Figure 1: Wire stripping length for a secure connection

Information:

The wire stripping length is not permitted to be more or less than 7 to 9 mm.

6 Cable holding force of contacts

To ensure secure contact of a cable with the terminal block, it is not permitted to be subjected to too much tension. If the cable holding force is exceeded, the cable will disconnect from the terminal block and result in a malfunction.

	Fine-stranded wires			Solid wires				With wire end sleeves	
Cable in mm ²	0.25	1.5	2.5	0.08	0.25	1.5	2.5	0.25	1.5
Standard specification (min. value in newtons)	12.5	40	50	4	12.5	40	50	12.5	40

Information:

Fine-stranded wires must be twisted in order to maintain the cable holding forces.

Use of wire end sleeves

In order to achieve an optimal cable holding force, the following points must be observed:

- Square crimping with the roughest possible surface should be carried out.
- The end of the wire end sleeve should not be cut in order to avoid a reduction of the cross section.
- No wires should protrude at the end of the sleeve.
- The wire end sleeve must be inserted completely to the end.
- The length of the wire end sleeve corresponds to the [wire stripping length](#).

7 Access for test probes

Each contact is equipped with an additional opening for using a test probe.

